

ISONV Insulated Conductor

Power Utilities



ISONV insulated down conductor is a specialized lightning protection down conductor that during operation may be subjected to impulse currents of up to 200 kA. ISONV is designed and tested to control separation distance and arcing. A semiconductive outer layer is used to minimize voltage gradients under lightning conditions.

FUNKCJE

Provides protection of equipment against lightning strike flashover by providing an insulated path to ground via an equivalent separation distance

Field terminated with separately ordered termination kits

SPECYFIKACJE

Prąd impulsowy (Iimp): 200 kA 10/350 μ s

Table 1/1

Numer katalogowy	Równoważna odległość separacji	Temperatura instalacji	Temperatura pracy
ISONV50	50 cm	-20 to 50 °C	-40 to 90 °C
ISONV70	70 cm	-20 to 50 °C	-40 to 90 °C

DODATKOWE INFORMACJE O PRODUKCIE

Available in 1 m increments up to 1,000 m.

OSTRZEŻENIE

Produkty nVent powinny być instalowane i używane wyłącznie zgodnie z instrukcjami i materiałami szkoleniowymi nVent. Instrukcje są dostępne na stronie www.nvent.com oraz u przedstawiciela działu obsługi klienta firmy nVent. Nieprawidłowa instalacja, niewłaściwe użycie, niewłaściwe zastosowanie lub inne nieprzestrzeganie instrukcji i ostrzeżeń nVent może spowodować nieprawidłowe działanie produktu, uszkodzenie mienia, poważne obrażenia ciała i śmierć i/lub utratę gwarancji.



Marki w naszej ofercie:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE