

STS MT Skin-Effect Tracing Wire



nVent RAYCHEM STS-MT Skin Effect Trace Heating Wires provide freeze protection and process temperature maintenance for embedded or long pipeline applications. Circuit lengths up to 15 miles/25 km are possible, minimizing the number of connection and power source locations. Suitable for applications up to a maximum 302 °F/150 °C and approved for use in hazardous and non-hazardous locations. The polyolefin outer jacket is ideal for heating pipelines transporting materials such as crude oil, VGO and phenol.

FUNKCJE

Custom engineered design, depending on the unique application type

Safe and efficient in operation: fully grounded system with zero electrical potential on pipe surfaces, can be used in Class 1 Division 2 and Zone 2 hazardous areas

Long circuit lengths (up to 15 miles/25 km), minimize operating and installation costs by reducing the required number of power supply points

Advanced control systems with multiple temperature inputs to adequately monitor and control longline heat tracing

Reliable during long life: entire circuit is encapsulated within rugged heat tubes and steel boxes

OKREŚLENIU SPECYFIKACJI

Max Power Output:	150 W/m
Max Maintain or Continuous Exposure Temperature, Power On:	150 °C
Min Installation Temperature:	-55 °C
Supply Voltage:	0 – 5000 V
Area Classification:	Non-Hazardous; Hazardous
Ground Path Type:	Brak
Outer Jacket Material:	Poliiolefin

Table 1/1

Numer katalogowy	Nazwa pozycji	Nominal Cable Weight	AWG Size	Min Bending Radius @ -55°C
F74409-000	STS-MT/13.50-WIRE #6AWG	200 g/m	6	65 mm
F93310-000	STS-MT/21.50-WIRE #4AWG	300 g/m	4	72 mm

Numer katalogowy	Nazwa pozycji	Nominal Cable Weight	AWG Size	Min Bending Radius @ -55°C
A42886-000	STS-MT/33.50-WIRE #2AWG	433 g/m	2	81 mm

OSTRZEŻENIE

Produkty nVent powinny być instalowane i używane wyłącznie zgodnie z instrukcjami i materiałami szkoleniowymi nVent. Instrukcje są dostępne na stronie www.nvent.com oraz u przedstawiciela działu obsługi klienta firmy nVent. Nieprawidłowa instalacja, niewłaściwe użycie, niewłaściwe zastosowanie lub inne nieprzestrzeganie instrukcji i ostrzeżeń nVent może spowodować nieprawidłowe działanie produktu, uszkodzenie mienia, poważne obrażenia ciała i śmierć i/lub utratę gwarancji.

Ameryka Północna

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Ameryka Łacińska

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT