


MI Series Inconel 600 HIQ Heating Cable



nVent RAYCHEM HIQ Inconel 600 sheathed mineral insulated (MI) series resistance trace heating cables provide freeze protection and process temperature maintenance. They can be used for exposure temperatures up to 700 °C (joint dependent) and typical power outputs up to 300 W/m. Alloy 600 sheath offers excellent corrosion resistance to a wide range of organic acids, alkalis and chloride stress-corrosion cracking. Approved for use in hazardous areas. Available 'fast track' as configured heating units.

FUNKCJE

Reduced total installed cost

Reduced power supply costs: lower start up currents compared with other technologies

Simple controls: current monitoring on series resistance provides instant visibility on critical circuits

Fast track/expedited service for configured heating units for eligible designs

Standard 550 °C continuous withstand temperature, with braze weld technology

Optional 700 °C continuous withstand temperature, with laser welded technology

Excellent corrosion resistance to a wide range of organic acids, alkalis and chloride stress-corrosion cracking

OKREŚLENIU SPECYFIKACJI

Min Cable Spacing:	25 mm
Max Power Output:	300 W/m
Max Continuous Exposure Temperature, Power Off:	680 °C
Min Installation Temperature:	-60 °C
Supply Voltage:	0 – 500 V
Area Classification:	Non-Hazardous; Hazardous
Sheath Material:	Inconel 600
Insulation Material:	Magnesium Oxide

Table 1/1

Numer katalogowy	Nominal Resistance @ 20°C	Zewnętrzna średnica
HIQ1M10K	10000 Ω/km	3.2 mm

Numer katalogowy	Nominal Resistance @ 20°C	Zewnętrzna średnica
HIQ1M4000	4000 Ω/km	3.2 mm
HIQ1M6300	6300 Ω/km	3.2 mm
HIQ1M2500	2500 Ω/km	3.4 mm
HIQ1M1600	1600 Ω/km	3.6 mm
HIQ1M1000	1000 Ω/km	3.9 mm
HIQ1M160	160 Ω/km	6.5 mm
HIQ1M630	630 Ω/km	4.3 mm
HIQ1M400	400 Ω/km	4.7 mm
HIQ1M250	250 Ω/km	5.3 mm

OSTRZEŻENIE

Produkty nVent powinny być instalowane i używane wyłącznie zgodnie z instrukcjami i materiałami szkoleniowymi nVent. Instrukcje są dostępne na stronie www.nvent.com oraz u przedstawiciela działu obsługi klienta firmy nVent. Nieprawidłowa instalacja, niewłaściwe użycie, niewłaściwe zastosowanie lub inne nieprzestrzeganie instrukcji i ostrzeżeń nVent może spowodować nieprawidłowe działanie produktu, uszkodzenie mienia, poważne obrażenia ciała i śmierć i/lub utratę gwarancji.

Ameryka Północna

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Ameryka Łacińska

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT