

nVent CADDY Speed Link SLK with Shot-Fire Bracket



CERTIFICATIONS



CARACTERÍSTICAS

Complete system includes wire, locking device and shot-fire bracket with pre-assembled drive pin from Powers Fasteners, Inc.

Quickly and easily attaches to concrete, steel or composite metal decking

Integrated pin installs easily using powder-actuated or single-shot gas-actuated tools

ICC-ES ESR-2024 evaluation report available for drive pin from DEWALT®

ESPECIFICAÇÕES

Static Load Safety Factor:	5:1
Acabamento:	Electrogalvanized
Material:	Aço; Liga de zinco; Polypropylene
Em conformidade com:	SMACNA HVAC-DCS

Table 1/2

Número de catálogo	Número do artigo	Wire Rope Diameter	Wire Rope Length	A	B	C
--------------------	------------------	--------------------	------------------	---	---	---

SLK2L2SF	196546	2 mm	2m	37.5 mm	7.6 mm	31.8 mm
SLK15L2SF	196518	1.5 mm	2m	37.5 mm	7.6 mm	31.8 mm
SLK2L3SF	196547	2 mm	3m	37.5 mm	7.6 mm	31.8 mm
SLK15L5SF	196520	1.5 mm	5m	37.5 mm	7.6 mm	31.8 mm
SLK15L1SF	196517	1.5 mm	1m	37.5 mm	7.6 mm	31.8 mm
SLK15L3SF	196519	1.5 mm	3m	37.5 mm	7.6 mm	31.8 mm

Table 2/2

Número de catálogo	Número do artigo	Static Load
SLK2L2SF	196546	440N
SLK15L2SF	196518	195N
SLK2L3SF	196547	440N
SLK15L5SF	196520	195N
SLK15L1SF	196517	195N
SLK15L3SF	196519	195N

Espessura (T): 12.5 mm

Largura (W): 19 mm

Altura (H): 55 mm

Ângulo (a): 90 ° Max

DETALHES ADICIONAIS DO PRODUTO


Uses Powers Fasteners, Inc. part number 50032.

Static load was established based on a 1" (25.4 mm) embedment depth and 3,000 psi (20.68 MPa) lightweight concrete. For variations in embedment and material please consult anchors.dewalt.com.

Pre-assembled drive pin from Powers Fasteners, Inc. works with Powers® C4CZ, Simpson® GCN-MEPKT, SPIT® P1000, P200, P2201, P3500 / PA3500, P35s, P45, P60, P7201, Sniper; Ramset® 721, Cobra, D45 / D60 / D60L, M70, SA270, T3SS, TS750P, TS60P, Viper; Hilti® DX35, DX350 / DX351 / DX36M, DX100 / DX200, DX460, DXA40, DXA41, DXE72 / DX400; Würth® Diva-1, BST-1, BST-2 or equivalent nailers.

For shot-fired supports in seismic design category D, E, or F, maximum load is the lesser of 90 lb (400 N) or the published load.

DIAGRAMAS



AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

+1 800 753 9221
Opção 1 – Apoio ao cliente
Opção 2 – Assistência
técnica

Europa

Países Baixos:
+31 800-0200135
França:
+33 800 901 793

Europa

Alemanha:
800 1890272
Outros países:
+31 13 5835404

APAC

Xangai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

