


# CABS Busbar Support Kit

## Power Utilities



### CERTIFICATIONS



### CARACTERÍSTICAS

For all busbar types

Improve bending resistance by interlocking or stacking two profiles

Quick and easy to install

Halogen free insulators

RoHS compliant

### ESPECIFICAÇÕES

Table 1/3

| Número de catálogo | Número do artigo | Typical Application Current Rating | Max Working Voltage, IEC (Ui) | Temperatura de trabalho | Busbars per Phase | Largura do barramento |
|--------------------|------------------|------------------------------------|-------------------------------|-------------------------|-------------------|-----------------------|
| CABS4-5TN-400      | 549310           | 400 – 4,500 A                      | 1,000 VAC,<br>1,500 VDC       | -40 to 130 °C           | 1 – 4             | 30 – 125 mm           |


Table 2/3

| Número de catálogo | Número do artigo | Busbar Thickness | Largura (W) | A      | B     | C      |
|--------------------|------------------|------------------|-------------|--------|-------|--------|
| CABS4-5TN-400      | 549310           | 5 mm             | 350 mm      | 300 mm | 75 mm | 325 mm |

Table 3/3

| Número de catálogo | Número do artigo | Peso unitário |
|--------------------|------------------|---------------|
| CABS4-5TN-400      | 549310           | 0.800 kg      |

## DIAGRAMAS



## AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em [www.nVent.com](http://www.nVent.com) e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE