

AMC-1H Mechanical Thermostat



nVent RAYCHEM AMC-1H is an ambient-sensing thermostat designed to control heat-tracing systems used for freeze protection in hazardous locations. Used to control a single heat tracing circuit or switch multiple circuits with a contactor, it has an adjustable set point.

RECURSOS

Simple to install and operate, single cable entry through 3/4"/19 mm NPT conduit hub

Energy saving, ambient sensing control thermostat

Adjustable set point: -15 °F to 140 °F/-9 °C to 60 °C

Electrical rating and switch: 22 A at 125/250/480 VAC, SPDT switch

Enclosure: NEMA 4, 7, 9 lacquer-coated cast aluminum housing, stainless steel hardware

Reliable during long life

ESPECIFICAÇÕES

Table 1/2

Número do catálogo	Nome do item	Material	NEMA Rating	Thermostat Type	Current Rating	Controller Temperature Setting
889067-000	AMC-1H	Alumínio	4, 7, 9	Mechanical Thermostat	22 A	-9 to 60 °C

Table 2/2

Número do catálogo	Nome do item	Max Measuring Range	Altura	Largura	Profundidade	Area Classification
889067-000	AMC-1H	71 °C	168 mm	114 mm	102 mm	Non-Hazardous, Hazardous

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

América Latina

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT