

Conector jumper de trilho, alimentação, estilo W, isolado



CARACTERÍSTICAS

Fornece resistência elétrica constante

Resistência superior à corrosão

A isolamento do condutor tem jaqueta de poliolefina cruzada de baixa emissão de fumaça

Instalação fácil com treinamento mínimo do instalador

Equipamento de instalação simples e altamente portátil

Igualmente utilizável em trilhos antigos, usados ou novos

Altamente durável

ESPECIFICAÇÕES

Estilo do terminal de ligação: W

Table 1/2


Número de catálogo	Isolado	Material	Acabamento	Tamanho do condutor	Length (L)	Diâmetro (Ø)
PBW12J00148 B	Sim	Copper, Ethylene Propylene Rubber, Aço	Bare, Copper Plated	2/0 Ropelay	1219.2mm	12.04 mm
PBJW22W1A10 3B	Sim	Copper, Ethylene Propylene Rubber	Bare, Tinned	250 kcmil Ropelay	2616.2mm	16.59 mm

Número de catálogo	Isolado	Material	Acabamento	Tamanho do condutor	Length (L)	Diâmetro (Ø)
PBJW22W1A127B	Sim	Copper, Ethylene Propylene Rubber	Bare, Tinned	250 kcmil Ropelay	3225.8mm	16.59 mm
PBJW22W1A28B	Sim	Copper, Ethylene Propylene Rubber	Bare, Tinned	250 kcmil Ropelay	711.2mm	16.59 mm
PBJW22W1A45B	Sim	Copper, Ethylene Propylene Rubber	Bare, Tinned	250 kcmil Ropelay	1143mm	16.59 mm
PBW12W002120B	SimEFS_PBW12W002120B	Copper, Ethylene Propylene Rubber	Bare, Tinned	250 kcmil Ropelay	3048mm	16.59 mm
PBW12W00230B	Sim	Copper, Ethylene Propylene Rubber	Bare, Tinned	250 kcmil Ropelay	762mm	16.59 mm
PBW12W00248B	Sim	Copper, Ethylene Propylene Rubber	Bare, Tinned	250 kcmil Ropelay	1219.2mm	16.59 mm
PBW12W00260B	Sim	Copper, Ethylene Propylene Rubber	Bare, Tinned	250 kcmil Ropelay	1524mm	16.59 mm
PBW13S001120B	Sim	Copper, Ethylene Propylene Rubber, Aço	Bare, Copper Plated	500 kcmil Ropelay	3048mm	23.42 mm
PBW13S00124B	Sim	Copper, Ethylene Propylene Rubber, Aço	Bare, Copper Plated	500 kcmil Ropelay	609.6mm	23.42 mm
PBW13S00160B	Sim	Copper, Ethylene Propylene Rubber, Aço	Bare, Copper Plated	500 kcmil Ropelay	1828.8mm	23.42 mm
PBW13S00172B	Sim	Copper, Ethylene Propylene Rubber, Aço	Bare, Copper Plated	500 kcmil Ropelay	1828.8mm	23.42 mm

Table 2/2

Número de catálogo	Espessura do isolamento
PBW12J00148B	2.3 mm
PBJW22W1A103B	2.4 mm
PBJW22W1A127B	2.4 mm
PBJW22W1A28B	2.4 mm
PBJW22W1A45B	2.4 mm
PBW12W002120B	2.4 mm
PBW12W00230B	2.4 mm
PBW12W00248B	2.4 mm
PBW12W00260B	2.4 mm
PBW13S001120B	2.7 mm
PBW13S00124B	2.7 mm
PBW13S00160B	2.7 mm
PBW13S00172B	2.7 mm

DIAGRAMAS



AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos

à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

+1 800 753 9221
Opção 1 – Apoio ao cliente
Opção 2 – Assistência
técnica

Europa

Países Baixos:
+31 800-0200135
França:
+33 800 901 793

Europa

Alemanha:
800 1890272
Outros países:
+31 13 5835404

APAC

Xangai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE