

MBJ Grounding and Bonding Braid, Tinned Copper



MBJ Grounding and Bonding Braids are a reliable and convenient grounding solution for applications that require flexibility and durability. The tinned copper ground braids with massivated palms come ready to install without any additional cutting, stripping, crimping or punching and do not require the addition of tin or crimped lugs. The proprietary manufacturing process optimizes the electrical contact between each wire and helps eliminate moisture issues in the palms, preventing corrosion and lengthening the useful life of the braid.

CERTIFICATIONS



CARACTERÍSTICAS

Complete range of earth/ground flexible connections from 6 - 100 mm² (11.84 - 197.35 kcmil) cross section and from 100 - 500 mm (3.937" - 19.685") length

Integral palm, without tin or crimped lugs for superior electrical contact and tensile strength resistance

Resistant to vibration and fatigue, reducing maintenance

Provides weight savings, material savings and lower impedance when compared to similar lugged cables with insulation

Ready to use out of the box, eliminates the need for cutting, stripping, crimping and punching

Quick and easy to install

Recommended by the EMC/EMI directives and less impedance than cables

EAC compliant

RoHS compliant

Compliant to ISO 6469-1 (Electrically propelled road vehicles - Part 1: Rechargeable energy storage system) - Section 6.2.2 Vibrations

ESPECIFICAÇÕES

Material: Copper

Em conformidade com: IEC® 60439.1; IEC® 61439.1

Acabamento: Tinned

Certification Details: UL® 467

Temperatura de trabalho: 105 °C Max

Table 1/2

Número de catálogo	Número do artigo	Ampacity	Espessura (T)	Corte transversal	Length (L)	Tamanho do orifício (HS)
MBJ6-150-6	556600	40A	1.1 mm	6mm ²	150mm	6.5 mm
MBJ6-200-6	563410	40A	1.1 mm	6mm ²	200mm	6.5 mm
MBJ10-200-6	556930	75A	1.1 mm	10mm ²	200mm	6.5 mm
MBJ16-100-6	563540	120A	1.5 mm	16mm ²	100mm	6.5 mm
MBJ16-100-8	556620	120A	1.5 mm	16mm ²	100mm	8.5 mm
MBJ10-300-6	556610	75A	1.1 mm	10mm ²	300mm	6.5 mm
MBJ16-200-6	563300	120A	1.5 mm	16mm ²	200mm	6.5 mm
MBJ16-200-8	556640	120A	1.5 mm	16mm ²	200mm	8.5 mm
MBJ25-100-10	556670	150A	1.9 mm	25mm ²	100mm	10.5 mm
MBJ30-100-10	556720	180A	2 mm	30mm ²	100mm	10.5 mm
MBJ16-150-6	563550	120A	1.5 mm	16mm ²	150mm	6.5 mm
MBJ16-150-8	556630	120A	1.5 mm	16mm ²	150mm	8.5 mm
MBJ16-250-8	556650	120A	1.5 mm	16mm ²	250mm	8.5 mm
MBJ25-150-10	556680	150A	1.9 mm	25mm ²	150mm	10.5 mm
MBJ35-100-10	556770	197A	2.1 mm	35mm ²	100mm	10.5 mm

Número de catálogo	Número do artigo	Ampacity	Espessura (T)	Corte transversal	Length (L)	Tamanho do orifício (HS)
MBJ16-300-6	563320	120A	1.5 mm	16mm ²	300mm	6.5 mm
MBJ16-300-8	556660	120A	1.5 mm	16mm ²	300mm	8.5 mm
MBJ25-200-10	556690	150A	1.9 mm	25mm ²	200mm	10.5 mm
MBJ25-200-12	563430	150A	1.9 mm	25mm ²	200mm	12.5 mm
MBJ25-200-6	563340	150A	1.9 mm	25mm ²	200mm	6.5 mm
MBJ25-200-8	555200	150A	1.9 mm	25mm ²	200mm	8.5 mm
MBJ30-150-10	556730	180A	2 mm	30mm ²	150mm	10.5 mm
MBJ35-150-10	556780	197A	2.1 mm	35mm ²	150mm	10.5 mm
MBJ50-100-10	556820	250A	2.5 mm	50mm ²	100mm	10.5 mm
MBJ16-500-8	556940	120A	1.5 mm	16mm ²	500mm	8.5 mm
MBJ25-250-10	556700	150A	1.9 mm	25mm ²	250mm	10.5 mm
MBJ30-200-10	556740	180A	2 mm	30mm ²	200mm	10.5 mm
MBJ25-300-10	556710	150A	1.9 mm	25mm ²	300mm	10.5 mm
MBJ25-300-8	555201	150A	1.9 mm	25mm ²	300mm	8.5 mm
MBJ25-500-10	556950	150A	1.9 mm	25mm ²	500mm	10.5 mm
MBJ30-250-10	556750	180A	2 mm	30mm ²	250mm	10.5 mm
MBJ35-200-10	556790	197A	2.1 mm	35mm ²	200mm	10.5 mm
MBJ30-300-10	556760	180A	2 mm	30mm ²	300mm	10.5 mm

Número de catálogo	Número do artigo	Ampacity	Espessura (T)	Corte transversal	Length (L)	Tamanho do orifício (HS)
MBJ30-500-10	556960	180A	2 mm	30mm ²	500mm	10.5 mm
MBJ35-250-10	556800	197A	2.1 mm	35mm ²	250mm	10.5 mm
MBJ35-300-10	556810	197A	2.1 mm	35mm ²	300mm	10.5 mm
MBJ35-500-10	556970	197A	2.1 mm	35mm ²	500mm	10.5 mm
MBJ50-150-10	556830	250A	2.5 mm	50mm ²	150mm	10.5 mm
MBJ35-250-25	565000	197A	3 mm	35mm ²	250mm	25.5 mm
MBJ50-200-10	556840	250A	2.5 mm	50mm ²	200mm	10.5 mm
MBJ50-200-12	563440	250A	2.5 mm	50mm ²	200mm	12.5 mm
MBJ50-200-16	563360	250A	2.5 mm	50mm ²	200mm	16.5 mm
MBJ50-200-18	563370	250A	2.5 mm	50mm ²	200mm	18.5 mm
MBJ50-200-6	563350	250A	2.5 mm	50mm ²	200mm	6.5 mm
MBJ50-250-10	556850	250A	2.5 mm	50mm ²	250mm	10.5 mm
MBJ50-300-10	556860	250A	2.5 mm	50mm ²	300mm	10.5 mm
MBJ50-300-16	563390	250A	2.5 mm	50mm ²	300mm	16.5 mm
MBJ50-300-18	563400	250A	2.5 mm	50mm ²	300mm	18.5 mm
MBJ50-300-6	563380	250A	2.5 mm	50mm ²	300mm	6.5 mm
MBJ50-500-10	556980	250A	2.5 mm	50mm ²	500mm	10.5 mm
MBJ50-500-12	563560	250A	2.5 mm	50mm ²	500mm	12.5 mm

Número de catálogo	Número do artigo	Ampacity	Espessura (T)	Corte transversal	Length (L)	Tamanho do orifício (HS)
MBJ70-300-22	563480	290A	3 mm	70mm ²	300mm	22.5 mm
MBJ70-300-10	563460	290A	3.4 mm	70mm ²	300mm	10.5 mm
MBJ70-300-12	563420	290A	3.4 mm	70mm ²	300mm	12.5 mm
MBJ70-300-16	563470	290A	3.4 mm	70mm ²	300mm	16.5 mm
MBJ70-300-6	563450	290A	3.4 mm	70mm ²	300mm	6.5 mm
MBJ70-500-10	563490	290A	3.4 mm	70mm ²	500mm	10.5 mm
MBJ100-250-16	563500	349A	4 mm	100mm ²	250mm	16.5 mm
MBJ100-250-30	563510	349A	4 mm	100mm ²	250mm	30.5 mm
MBJ100-500-16	563520	349A	4 mm	100mm ²	500mm	16.5 mm
MBJ100-500-30	563530	349A	4 mm	100mm ²	500mm	30.5 mm

Table 2/2

Número de catálogo	Número do artigo	A	B	Peso unitário	Certifications
MBJ6-150-6	556600	11 mm	18 mm	0.01 kg	UL, CE, ERIFLEX MBJ, Bureau Veritas, RoHS, cUL, UKCA, ERIFLEX MBJ
MBJ6-200-6	563410	11 mm	18 mm	0.02 kg	UKCA, ERIFLEX MBJ, RoHS, UL, CE, ERIFLEX MBJ, Bureau Veritas, cUL
MBJ10-200-6	556930	11 mm	18 mm	0.02 kg	RoHS, UL, CE, ERIFLEX MBJ, Bureau Veritas, cUL, UKCA, ERIFLEX MBJ

Número de catálogo	Número do artigo	A	B	Peso unitário	Certifications
MBJ16-100-6	563540	15 mm	20 mm	0.02 kg	RoHS, UL, CE, ERIFLEX MBJ, Bureau Veritas, cUL, UKCA, ERIFLEX MBJ
MBJ16-100-8	556620	15 mm	20 mm	0.02 kg	UKCA, ERIFLEX MBJ, UL, CE, ERIFLEX MBJ, Bureau Veritas, RoHS, cUL
MBJ10-300-6	556610	11 mm	18 mm	0.03 kg	UKCA, ERIFLEX MBJ, UL, CE, ERIFLEX MBJ, Bureau Veritas, RoHS, cUL
MBJ16-200-6	563300	15 mm	20 mm	0.03 kg	UKCA, ERIFLEX MBJ, UL, CE, ERIFLEX MBJ, Bureau Veritas, RoHS, cUL
MBJ16-200-8	556640	15 mm	20 mm	0.03 kg	cUL, UL, CE, ERIFLEX MBJ, Bureau Veritas, UKCA, ERIFLEX MBJ, RoHS
MBJ25-100-10	556670	20 mm	28 mm	0.03 kg	UKCA, ERIFLEX MBJ, UL, CE, ERIFLEX MBJ, Bureau Veritas, RoHS, cUL
MBJ30-100-10	556720	22 mm	28 mm	0.03 kg	UL, CE, ERIFLEX MBJ, Bureau Veritas, RoHS, cUL, UKCA, ERIFLEX MBJ
MBJ16-150-6	563550	15 mm	20 mm	0.04 kg	cUL, UL, CE, ERIFLEX MBJ, Bureau Veritas, UKCA, ERIFLEX MBJ, RoHS
MBJ16-150-8	556630	15 mm	20 mm	0.04 kg	RoHS, UL, CE, ERIFLEX MBJ, Bureau Veritas, cUL, UKCA, ERIFLEX MBJ

Número de catálogo	Número do artigo	A	B	Peso unitário	Certifications
MBJ16-250-8	556650	15 mm	20 mm	0.04 kg	RoHS, UL, CE, ERIFLEX MBJ, Bureau Veritas, cUL, UKCA, ERIFLEX MBJ
MBJ25-150-10	556680	20 mm	28 mm	0.04 kg	cUL, UL, CE, ERIFLEX MBJ, Bureau Veritas, UKCA, ERIFLEX MBJ, RoHS
MBJ35-100-10	556770	22 mm	28 mm	0.04 kg	UL, CE, ERIFLEX MBJ, Bureau Veritas, RoHS, cUL, UKCA, ERIFLEX MBJ
MBJ16-300-6	563320	15 mm	20 mm	0.05 kg	UKCA, ERIFLEX MBJ, UL, CE, ERIFLEX MBJ, Bureau Veritas, RoHS, cUL
MBJ16-300-8	556660	15 mm	20 mm	0.05 kg	cUL, UL, CE, ERIFLEX MBJ, Bureau Veritas, UKCA, ERIFLEX MBJ, RoHS
MBJ25-200-10	556690	20 mm	28 mm	0.05 kg	RoHS, UL, CE, ERIFLEX MBJ, Bureau Veritas, cUL, UKCA, ERIFLEX MBJ
MBJ25-200-12	563430	20 mm	28 mm	0.05 kg	UKCA, ERIFLEX MBJ, UL, CE, ERIFLEX MBJ, Bureau Veritas, RoHS, cUL
MBJ25-200-6	563340	20 mm	28 mm	0.05 kg	cUL, UL, CE, ERIFLEX MBJ, Bureau Veritas, UKCA, ERIFLEX MBJ, RoHS
MBJ25-200-8	555200	20 mm	28 mm	0.05 kg	UL, CE, ERIFLEX MBJ, Bureau Veritas, cUL

Número de catálogo	Número do artigo	A	B	Peso unitário	Certifications
MBJ30-150-10	556730	22 mm	28 mm	0.05 kg	UKCA, ERIFLEX MBJ, RoHS, UL, CE, ERIFLEX MBJ, Bureau Veritas, cUL
MBJ35-150-10	556780	22 mm	28 mm	0.05 kg	UKCA, ERIFLEX MBJ, RoHS, UL, CE, ERIFLEX MBJ, Bureau Veritas, cUL
MBJ50-100-10	556820	28 mm	33 mm	0.05 kg	UKCA, ERIFLEX MBJ, RoHS, UL, CE, ERIFLEX MBJ, Bureau Veritas, cUL
MBJ16-500-8	556940	15 mm	20 mm	0.08 kg	RoHS, UL, CE, ERIFLEX MBJ, Bureau Veritas, cUL, UKCA, ERIFLEX MBJ
MBJ25-250-10	556700	20 mm	28 mm	0.06 kg	cUL, UL, CE, ERIFLEX MBJ, Bureau Veritas, RoHS, UKCA, ERIFLEX MBJ
MBJ30-200-10	556740	22 mm	28 mm	0.06 kg	cUL, RoHS, UKCA, ERIFLEX MBJ, UL, CE, ERIFLEX MBJ, Bureau Veritas
MBJ25-300-10	556710	20 mm	28 mm	0.08 kg	UKCA, ERIFLEX MBJ, UL, CE, ERIFLEX MBJ, Bureau Veritas, cUL, RoHS
MBJ25-300-8	555201	20 mm	28 mm	0.08 kg	UL, CE, ERIFLEX MBJ, Bureau Veritas, cUL
MBJ25-500-10	556950	20 mm	28 mm	0.13 kg	cUL, RoHS, UKCA, ERIFLEX MBJ, UL, CE, ERIFLEX MBJ, Bureau Veritas
MBJ30-250-10	556750	22 mm	28 mm	0.07 kg	UL, CE, ERIFLEX MBJ, Bureau Veritas, RoHS, cUL, UKCA, ERIFLEX MBJ


Número de catálogo	Número do artigo	A	B	Peso unitário	Certifications
MBJ35-200-10	556790	22 mm	28 mm	0.07 kg	cUL, RoHS, UKCA, ERIFLEX MBJ, UL, CE, ERIFLEX MBJ, Bureau Veritas
MBJ30-300-10	556760	22 mm	28 mm	0.09 kg	UKCA, ERIFLEX MBJ, RoHS, UL, CE, ERIFLEX MBJ, Bureau Veritas, cUL
MBJ30-500-10	556960	22 mm	28 mm	0.15 kg	cUL, RoHS, UKCA, ERIFLEX MBJ, UL, CE, ERIFLEX MBJ, Bureau Veritas
MBJ35-250-10	556800	22 mm	28 mm	0.09 kg	UL, CE, ERIFLEX MBJ, Bureau Veritas, RoHS, cUL, UKCA, ERIFLEX MBJ
MBJ35-300-10	556810	22 mm	28 mm	0.11 kg	cUL, RoHS, UKCA, ERIFLEX MBJ, UL, CE, ERIFLEX MBJ, Bureau Veritas
MBJ35-500-10	556970	22 mm	28 mm	0.18 kg	UL, CE, ERIFLEX MBJ, Bureau Veritas, RoHS, cUL, UKCA, ERIFLEX MBJ
MBJ50-150-10	556830	28 mm	33 mm	0.08 kg	cUL, RoHS, UKCA, ERIFLEX MBJ, UL, CE, ERIFLEX MBJ, Bureau Veritas
MBJ35-250-25	565000	40 mm	45 mm	0.09 kg	UKCA, ERIFLEX MBJ, RoHS, UL, CE, ERIFLEX MBJ, Bureau Veritas, cUL
MBJ50-200-10	556840	28 mm	33 mm	0.12 kg	UL, CE, ERIFLEX MBJ, Bureau Veritas, RoHS, cUL, UKCA, ERIFLEX MBJ
MBJ50-200-12	563440	28 mm	33 mm	0.12 kg	UKCA, ERIFLEX MBJ, RoHS, UL, CE, ERIFLEX MBJ, Bureau Veritas, cUL

Número de catálogo	Número do artigo	A	B	Peso unitário	Certifications
MBJ50-200-16	563360	28 mm	33 mm	0.11 kg	cUL, RoHS, UKCA, ERIFLEX MBJ, UL, CE, ERIFLEX MBJ, Bureau Veritas
MBJ50-200-18	563370	28 mm	33 mm	0.11 kg	UL, CE, ERIFLEX MBJ, Bureau Veritas, RoHS, cUL, UKCA, ERIFLEX MBJ
MBJ50-200-6	563350	28 mm	33 mm	0.12 kg	UKCA, ERIFLEX MBJ, RoHS, UL, CE, ERIFLEX MBJ, Bureau Veritas, cUL
MBJ50-250-10	556850	28 mm	33 mm	0.13 kg	cUL, RoHS, UKCA, ERIFLEX MBJ, UL, CE, ERIFLEX MBJ, Bureau Veritas
MBJ50-300-10	556860	28 mm	33 mm	0.15 kg	UL, CE, ERIFLEX MBJ, Bureau Veritas, RoHS, cUL, UKCA, ERIFLEX MBJ
MBJ50-300-16	563390	28 mm	33 mm	0.15 kg	UKCA, ERIFLEX MBJ, RoHS, UL, CE, ERIFLEX MBJ, Bureau Veritas, cUL
MBJ50-300-18	563400	28 mm	33 mm	0.14 kg	cUL, RoHS, UKCA, ERIFLEX MBJ, UL, CE, ERIFLEX MBJ, Bureau Veritas
MBJ50-300-6	563380	28 mm	33 mm	0.15 kg	UL, CE, ERIFLEX MBJ, Bureau Veritas, RoHS, cUL, UKCA, ERIFLEX MBJ
MBJ50-500-10	556980	28 mm	33 mm	0.26 kg	UKCA, ERIFLEX MBJ, RoHS, UL, CE, ERIFLEX MBJ, Bureau Veritas, cUL
MBJ50-500-12	563560	28 mm	33 mm	0.26 kg	cUL, RoHS, UKCA, ERIFLEX MBJ, UL, CE, ERIFLEX MBJ, Bureau Veritas

Número de catálogo	Número do artigo	A	B	Peso unitário	Certifications
MBJ70-300-22	563480	40 mm	45 mm	0.2 kg	cUL, RoHS, UKCA, ERIFLEX MBJ, UL, CE, ERIFLEX MBJ, Bureau Veritas
MBJ70-300-10	563460	28 mm	33 mm	0.21 kg	cUL, RoHS, UKCA, ERIFLEX MBJ, UL, CE, ERIFLEX MBJ, Bureau Veritas
MBJ70-300-12	563420	28 mm	33 mm	0.21 kg	UL, CE, ERIFLEX MBJ, Bureau Veritas, RoHS, cUL, UKCA, ERIFLEX MBJ
MBJ70-300-16	563470	28 mm	33 mm	0.2 kg	UKCA, ERIFLEX MBJ, RoHS, UL, CE, ERIFLEX MBJ, Bureau Veritas, cUL
MBJ70-300-6	563450	28 mm	33 mm	0.21 kg	UL, CE, ERIFLEX MBJ, Bureau Veritas, RoHS, cUL, UKCA, ERIFLEX MBJ
MBJ70-500-10	563490	28 mm	33 mm	0.34 kg	UKCA, ERIFLEX MBJ, RoHS, UL, CE, ERIFLEX MBJ, Bureau Veritas, cUL
MBJ100-250-16	563500	40 mm	55 mm	0.25 kg	cUL, UL, CE, ERIFLEX MBJ, Bureau Veritas, UKCA, ERIFLEX MBJ, RoHS
MBJ100-250-30	563510	40 mm	55 mm	0.25 kg	RoHS, UL, CE, ERIFLEX MBJ, Bureau Veritas, cUL, UKCA, ERIFLEX MBJ
MBJ100-500-16	563520	40 mm	42.5 mm	0.51 kg	UKCA, ERIFLEX MBJ, UL, CE, ERIFLEX MBJ, Bureau Veritas, RoHS, cUL

Número de catálogo	Número do artigo	A	B	Peso unitário	Certifications
MBJ100-500-30	563530	40 mm	55 mm	0.51 kg	cUL, UL, CE, ERIFLEX MBJ, Bureau Veritas, UKCA, ERIFLEX MBJ, RoHS

DIAGRAMAS



AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

+1 800 753 9221
Opção 1 – Apoio ao cliente
Opção 2 – Assistência técnica

Europa

Países Baixos:
+31 800-0200135
França:
+33 800 901 793

Europa

Alemanha:
800 1890272
Outros países:
+31 13 5835404

APAC

Xangai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE