

Condutor Flexbus nVent ERIFLEX

Concessionárias de energia



nVent ERIFLEX Flexbus Conductor is ready-to-use from one side with direct connection to busbar or circuit-breaker palm. It is an innovative and patented connection solution between two pieces of electrical equipment (such as a transformer, switchboard or generator). Flexbus Advanced maintains a high level of reliability and creates an easy and customizable connection on-site without additional design study, specific specialized workforce or expensive tools. The Flexbus Conductor is insulated with a low-smoke, halogen-free, flame-retardant (LSHFFR), high-temperature and class II material. Flexbus Conductor is a flexible, copper-plated, aluminum flat braid with insulation available from 2 to 10 meters length and under different cross section for 500A to 4500A applications. It allows for connection from the power supply to switchgear with only one conductor per phase up to 1600kVA and with two conductors per phase up to 3150kVA.

CERTIFICAÇÕES



RECURSOS

Flexible insulated copper-plated, aluminum flat braid

Better current/ampacity than cable due to skin effect

Much more flexible than cable

No bending radius to respect

Ready-to-use from one side with direct connection on busbar or circuit breaker palm

Only one conductor per phase from 400kVA (560 A) to 1600kVA (2250 A) and two conductors per phase for 2000kVA (2800 A) to 3150kVA (4435 A)

ESPECIFICAÇÕES

Table 1/5						
Número do catálogo	Número do artigo	Comprimento 1 (L1)	Length 2 (L2)	Connector Finish	Insulation Elongation	Espessura do isolamento
FLEXCOND128 OL10	508058	10,000 mm	100 mm	Estanhado	500 % Min	2.5 – 3.5 mm

Table 2/5						
Número do catálogo	Número do artigo	Rigidez dielétrica	Euroclass CPR	Halogen Free Rating	Low Smoke Rating	Mechanical Resistance Rating
FLEXCOND128 OL10	508058	20 kV/mm	Eca - s2, d2, a3	UL® 2885, IEC® 60754-1, IEC® 62821-2	IEC® 61034-2, ISO 5659-2, UL® 2885	IK09

Table 3/5						
Número do catálogo	Número do artigo	UV Resistance Rating	Nominal Voltage, IEC	Temperatura de trabalho	ΔT 60 K	Largura 1 (W1)
FLEXCOND128 OL10	508058	UL® 2556, UL® 854, IEC® 60364: AN3 Level	1,000 VAC, 1,500 VDC	-50 to 115 °C	1,984 A	108 mm

Table 4/5						
Número do catálogo	Número do artigo	Width 2 (W2)	Altura 1 (H1)	Height 2 (H2)	Peso da unidade	A
FLEXCOND128 OL10	508058	100 mm	31.1 mm	18 mm	56.800 kg	50 mm


Table 5/5						
Número do catálogo	Número do artigo	B	C	D	2 Bar Current Coefficient, Non-Symmetric	2 Bar Current Coefficient, Symmetric
FLEXCOND128 OL10	508058	50 mm	25 mm	25 mm	1.48	2

**Installation
Standard:**

AS 3008;BS 7671;CEI 64-8;CSN;DIN VDE 0100;HD 384;IEC® 60364;NBR 5410;NEN 1010;NFC 15-100;NIBT-NIN;NP (2002);ÖNORM;REBT;RGIE-AREI

ADDITIONAL PRODUCT DETAILS

Optional extender available for more connection possibilities.



AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE