

nVent CADDY Speed Link Catenary Cable Spool



CARACTERISTICAS

Used for installing custom lengths of catenary cable with two locking devices

Spool with nVent CADDY Speed Link steel wire

Wire rope constructed from 7 bundles of 19 strands each of steel aircraft wire

ESPECIFICAÇÕES

Acabamento: Hot-Dip Galvanized

Material: Aço

Table 1/1

Número de catálogo	Número do artigo	Wire Rope Diameter	Wire Rope Length	Ângulo (a)
SLC6CTO	196819	6 mm		60 ° Max
SLC6L50	196821	6 mm	50m	60 ° Max

DETALHES ADICIONAIS DO PRODUTO


Static load 1 represents a point load in the center of the catenary installation. Static load 2 represents a two or three point distributed load on the catenary installation. Static load 3 represents a four or more point distributed load on the catenary installation.

Preload of the wire rope must be applied using Catenary Tensioning Tool.

Cut-to-order (CTO) lengths orderable in meter increments.

Horizontal Intallation		
Preload	1000 N	450 N
Static Load 1 (F1)	490 N	590 N
Static Load 2 (F2)	880 N	1080 N
Static Load 3 (F3)	980 N	1180 N
Vertical Installation		
Static Load 4 (F4)	4440 N	

DIAGRAMAS



AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

+1 800 753 9221
Opção 1 – Apoio ao cliente
Opção 2 – Assistência
técnica

Europa

Países Baixos:
+31 800-0200135
França:
+33 800 901 793

Europa

Alemanha:
800 1890272
Outros países:
+31 13 5835404

APAC

Xangai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

