

nVent CADDY Speed Link Catenary Kit



CARACTERISTICAS

Kit includes precut length of fuse-cut cable to avoid fraying, pre-assembled hook end fitting and tool-free locking device to save installation time

Fastens to the building structure by looping around and hooking to wire rope

Hook end-fitting easily attaches to eye nut

Spring latch helps provide secure connection

ESPECIFICAÇÕES

Wire Rope Diameter: 6 mm

Acabamento: Electrogalvanized; Hot-Dip Galvanized

Table 1/2

Número de catálogo	Número do artigo	Material	Wire Rope Length	A	B	C
SLK6L10	196801	Steel, Liga de zinco, Polypropylene	10m	75 mm	40 mm	15 mm
SLK6L15	196802	Steel, Liga de zinco, Polypropylene	15m	75 mm	40 mm	15 mm
SLK6L20	196803	Steel, Liga de zinco, Polypropylene	20m	75 mm	40 mm	15 mm

Número de catálogo	Número do artigo	Material	Wire Rope Length	A	B	C
SLK6L25	196804	Steel, Liga de zinco, Polypropylene	25m	75 mm	40 mm	15 mm
SLK6L30	196805	Steel, Liga de zinco, Polypropylene	30m	75 mm	40 mm	15 mm
SLK6L40	196806	Steel, Liga de zinco, Polypropylene	40m	75 mm	40 mm	15 mm
SLK6L5	196800	Steel, Liga de zinco, Polypropylene	5m	75 mm	40 mm	15 mm
SLK6L50	196807	Steel, Liga de zinco, Polypropylene	50m	75 mm	40 mm	15 mm

Table 2/2

Número de catálogo	Número do artigo	Altura (H)	Largura (W)	Espessura (T)	Ângulo (a)
SLK6L10	196801	108 mm	41 mm	30 mm	60 ° Max
SLK6L15	196802	108 mm	41 mm	30 mm	60 ° Max
SLK6L20	196803	108 mm	41 mm	30 mm	60 ° Max
SLK6L25	196804	108 mm	41 mm	30 mm	60 ° Max
SLK6L30	196805	108 mm	41 mm	30 mm	60 ° Max
SLK6L40	196806	108 mm	41 mm	30 mm	60 ° Max
SLK6L5	196800	108 mm	41 mm	30 mm	60 ° Max
SLK6L50	196807	108 mm	41 mm	30 mm	60 ° Max

DETALHES ADICIONAIS DO PRODUTO


Wire Rope Length is measured from the end of the wire rope to the hook side of the swage.

Static load 1 represents a point load in the center of the catenary installation. Static load 2 represents a two or three point distributed load on the catenary installation. Static load 3 represents a four or more point distributed load on the catenary installation.

Preload of the wire rope must be applied using Catenary Tensioning Tool.

Horizontal Installation		
Preload	1000 N	450 N
Static Load 1 (F1)	490 N	590 N
Static Load 2 (F2)	880 N	1080 N
Static Load 3 (F3)	980 N	1180 N
Vertical Installation		
Static Load 4 (F4)	4440 N	

DIAGRAMAS



AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

+1 800 753 9221

Opção 1 – Apoio ao cliente

Opção 2 – Assistência
técnica

Europa

Países Baixos:

+31 800-0200135

França:

+33 800 901 793

Europa

Alemanha:

800 1890272

Outros países:

+31 13 5835404

APAC

Xangai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



O nosso forte portefólio de marcas:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRachte

