

MI Series Bare Copper Heating Cable



nVent RAYCHEM mineral insulated (MI) series resistance trace heating cables are used for low temperature maintenance applications such as long pipeline heating, condensation prevention and ramp heating. Copper sheath with continuous exposure temperatures to 392 °F/200 °C and typical power outputs to 20 W/ft (65 W/m). Approved for use in hazardous areas.

RECURSOS

Reduced total installed cost

Reduced power supply costs: lower start up currents compared with other technologies

Simple controls: current monitoring on series resistance provides instant visibility on critical circuits

Fast track/expedited service not available for configured heating units

ESPECIFICAÇÕES

Min Cable Spacing:	25 mm
Max Power Output:	65 W/m
Max Continuous Exposure Temperature, Power Off:	200 °C
Min Installation Temperature:	-60 °C
Sheath Material:	Cobre
Area Classification:	Non-Hazardous; Hazardous
Insulation Material:	Magnesium Oxide

Table 1/1

Número do catálogo	Supply Voltage	Nominal Resistance @ 20°C	Diâmetro externo
HCC1M1.08	0 – 500 V	1.08 Ω/km	8.3 mm
HCC1M1.72	0 – 500 V	1.72 Ω/km	7.3 mm
HCC1M2.87	0 – 500 V	2.87 Ω/km	6.4 mm

Número do catálogo	Supply Voltage	Nominal Resistance @ 20°C	Diâmetro externo
HCC1M4	0 – 500 V	4 Ω/km	5.9 mm
HCC1M7	0 – 500 V	7 Ω/km	5.3 mm
HCC1M11	0 – 500 V	11 Ω/km	4.9 mm
HCC1M17	0 – 500 V	17 Ω/km	4.6 mm
HCC1M25	0 – 500 V	25 Ω/km	3.7 mm
HCC1M40	0 – 500 V	40 Ω/km	3.4 mm
HCC1M63	0 – 500 V	63 Ω/km	3.2 mm
HCH1L1250	0 – 300 V	1250 Ω/km	2.8 mm
HCH1L2000	0 – 300 V	2000 Ω/km	2.8 mm
HCC1M88	0 – 500 V	88 Ω/km	3 mm
HCH1M100	0 – 500 V	100 Ω/km	5.2 mm
HCH1M800	0 – 500 V	800 Ω/km	3.5 mm
HCH1M140	0 – 500 V	140 Ω/km	4.9 mm
HCH1M630	0 – 500 V	630 Ω/km	4 mm
HCH1M450	0 – 500 V	450 Ω/km	4 mm
HCH1M315	0 – 500 V	315 Ω/km	4.3 mm
HCH1M220	0 – 500 V	220 Ω/km	4.5 mm

ADDITIONAL PRODUCT DETAILS

Max Power Output: Depending on application, max power outputs up to 40W/ft are permitted.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East,

Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

América Latina

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT