

MONI-PT100-4/20MA Sensor Assembly for Hazardous Areas



nVent RAYCHEM MONI-PT100-4/20MA is a PT100 sensor connected to a 4-20 mA transmitter built into a black glass fiber reinforced polyester junction box. Suitable for hazardous areas.

RECURSOS

Simple and fast to install: built in a black glass fiber reinforced polyester junction box with blue M20 cable gland

Temperature measuring range: -50 °C to +250 °C

ESPECIFICAÇÕES

Table 1/2

Número do catálogo	Nome do item	Housing Material	Instalação	Max Measuring Range	Operating Temperature	Fixed Cable to Sensor
704058-000	PT100-4/20MA	Glass Fibre Reinforced Polyester	Bracket	250 °C	-20 to 55 °C	Sim

Table 2/2

Número do catálogo	Nome do item	Comprimento do cabo	Sensor Tip Diameter
704058-000	PT100-4/20MA	2 m	3 mm

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

**Europe, Middle East,
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

América Latina

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT