

# TT1100-OHP-THIN Water Sensing Cable for Insulated Pipe, Modular



nVent RAYCHEM TraceTek TT1100-OHP-THIN is a range of fixed length, small diameter water sensing cables for use on insulated pipes.

## RECURSOS

Advanced technology: supplied with a porous fluoropolymer outer fiber braid surrounding the base TT1100 sensor cable

Simple and fast to install: the fiber overbraid provides superior flexibility, with factory fitted plastic connectors

Easy to design: modular, fixed lengths

Mechanically strong: fluoropolymer outer braid withstands compression forces associated with the use of sheet metal lagging surrounding the pipe insulation

## ESPECIFICAÇÕES

|                                   |                                       |
|-----------------------------------|---------------------------------------|
| <b>Diâmetro externo:</b>          | 6,8 mm                                |
| <b>Max Operating Temperature:</b> | 80 °C                                 |
| <b>Detection Method:</b>          | Raychem Conductive-Polymer Technology |
| <b>Model:</b>                     | Sensing Cable                         |
| <b>Detection:</b>                 | Water                                 |

Table 1/1

| Número do catálogo | Nome do item            | Comprimento |
|--------------------|-------------------------|-------------|
| P000001254         | TT1100-OHP-THIN-15M-PC  | 15 m        |
| P000001257         | TT1100-OHP-THIN-1M-PC   | 1 m         |
| P000001251         | TT1100-OHP-THIN-100M-PC | 100 m       |

| Número do catálogo | Nome do item            | Comprimento |
|--------------------|-------------------------|-------------|
| P000001255         | TT1100-OHP-THIN-7.5M-PC | 7.5 m       |
| P000001253         | TT1100-OHP-THIN-30M-PC  | 30 m        |
| P000001256         | TT1100-OHP-THIN-3M-PC   | 3 m         |
| P000001252         | TT1100-OHP-THIN-50M-PC  | 50 m        |

## AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em [www.nVent.com](http://www.nVent.com) e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

### América do Norte

Tel +1.800.545.6258  
Fax +1.800.527.5703  
[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

### Europe, Middle East, Africa

Tel +32.16.213.511  
Fax +32.16.213.604  
[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

### Asia Pacific

Tel +86.21.2412.1688  
Fax +86.21.5426.3167  
[cn.thermal.info@nvent.com](mailto:cn.thermal.info@nvent.com)

### América Latina

Tel +1.713.868.4800  
Fax +1.713.868.2333  
[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

Our powerful portfolio of brands:

**RAYCHEM PYROTENAX TRACER NUHEAT**