


VPL Power-Limiting Heating Cable



nVent RAYCHEM VPL power-limiting trace heating cables are mainly used for process temperature maintenance applications that require steam cleaning, up to 455 °F/235 °C and withstand intermittent exposure to 500 °F/260 °C. VPL offers high power output at high temperatures, which can reduce the number of heating cables required and is hazardous area approved. Also suitable for freeze protection. The fluoropolymer outer jacket (-CT) provides high chemical resistance against aggressive organics and corrosives.

RECURSOS

Efficient system design: high power output at elevated temperatures reduces heating cable required, flat P-T curve results in lower T start up and power equipment costs, longer circuit lengths due to larger cross section conductors

Maximum circuit length further increases when operating at higher voltages: reducing the number of circuits and power supply equipment

Fast installation: cut-to-length, multiple overlaps allowed, meter markings, user-friendly connections kits

Safe and efficient in operation: no overheating, uniform pipe temperatures, energy saving technology

Reliable during long life: 10 year product warranty available, maintenance free

ESPECIFICAÇÕES

Max Continuous Exposure Temperature, Power Off:	260 °C
Max Cumulative Hours for Intermittent Exposure:	1000 h
Min Installation Temperature:	-60 °C
Ground Path Type:	Braid
Area Classification:	Non-Hazardous; Hazardous
Outer Jacket Material:	High Temperature Fluoropolymer

Table 1/1

Número do catálogo	Nome do item	Supply Voltage	Nominal Power Output @ 10°C, 230V	Nominal Power Output @ 10°C, 400V	Max Maintain or Continuous Exposure Temperature, Power On
068380-000	15VPL2-CT	200 – 277 V	45 W/m		230 °C

Número do catálogo	Nome do item	Supply Voltage	Nominal Power Output @ 10°C, 230V	Nominal Power Output @ 10°C, 400V	Max Maintain or Continuous Exposure Temperature, Power On
451828-000	5VPL2-CT	200 – 277 V	15 W/m		235 °C
589252-000	20VPL2-CT	200 – 240 V	61 W/m		150 °C
892652-000	10VPL2-CT	200 – 277 V	30 W/m		220 °C
P000000678	5VPL4-CT	400 – 480 V		12 W/m	230 °C
P000000679	10VPL4-CT	400 – 480 V		24 W/m	205 °C
P000000680	15VPL4-CT	400 – 480 V		36 W/m	170 °C
P000000681	20VPL4-CT	400 – 480 V		49 W/m	150 °C

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

América Latina

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT