

XL-Trace Low Smoke Zero Halogen Self-Regulating Heating Cable



nVent RAYCHEM XL-Trace self-regulating trace heating cables provide energy efficient and easy to use solutions for pipe freeze protection and flow maintenance in grease waste lines. Developed with low smoke zero halogen (LSZH) materials, to ensure the safest solution for modern building design.

RECURSOS

Unparalleled safety, low smoke zero halogen construction: up to 90% less smoke emissions and improved self-extinguishing properties

Simple to design: long circuit lengths to 215 m, for fewer power connections and faster installation

Easy to install: highly flexible cable, cut to length, meter marks, fast RayClic cold connection system

Energy efficient and safe: self-regulating cable, advanced energy saving controls, major savings when used with proportional ambient sensing controller (PASC), no cable overheating possible, low smoke zero halogen

Reliable during long life: 10 year product warranty available, UV resistant, colorfast, maintenance free

ESPECIFICAÇÕES

Nominal Thickness:	6,8 mm
Nominal Width:	13,8 mm
Supply Voltage:	220 – 240 V
Min Installation Temperature:	-40 °C
Ground Path Type:	Braid
Outer Jacket Material:	Low Smoke Zero Halogen
Conductor Material:	Nickel-Plated Copper

Table 1/1

Número do catálogo	Nome do item	Nominal Power Output @ 5°C, 230V	Max Circuit Length	Cor
P000002113	10XL2-ZH	10 W/m	238 m	Plum

Número do catálogo	Nome do item	Nominal Power Output @ 5°C, 230V	Max Circuit Length	Cor
P000002114	15XL2-ZH	15 W/m	188 m	Verde
P000002115	26XL2-ZH	26 W/m	142 m	Blue
P000002116	31XL2-ZH	31 W/m	114 m	Roxo

ADDITIONAL PRODUCT DETAILS

Circuit Lengths are based on a 20 A C-Type characteristic circuit protection device, Power on at +5 °C.

When selecting the heating circuit length, the maximum switching capacity of the respective controller must be taken into account.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East,

Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

América Latina

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT