

# **nVent ERIFLEX FleXbus Foam Barrier FBS**

## **Data Solutions**



#### **CERTIFICATIONS**











#### CARACTERISTICI

Easy access for difficult-to-reach openings

Age, smoke and damp resistant

Re-enterable and repairable

Excellent adhesion

No backing material required

F-rating / E-rating up to 2 hours

T-rating / I-rating up to 2 hours

Expands up to 5 times of its volume

### **SPECIFICAȚII**

15 - 30°C **Installation Temperature:** Volume: 380ml Color: Red; Brown Width: 450mm max

500mm max Height: Approx. Cure Time: 90s min

Table 1/2								
Număr de catalog	Article Number	Complies With	Density	Flammability Rating	Sound Transmission Class	Volume Yield		
FLEXFOAMBAR UL	508153	ASTM E 84 (UL 723), ASTM E 814 (UL 1479)				1.9l max		
FLEXFOAMBAR RIER	508150	EN 13501-1, EN 1366-3	215 min	DIN 4102 (B2)	43.5 - 66dB(A)	2.1l max		

Table 2/2							
Număr de catalog	Article Number	Unit Weight	Certifications				
FLEXFOAMBARUL	508153	0.72kg	CE, cULus Classified, ESTI ERIFLEX FleXbus, RoHS				
FLEXFOAMBARRIER	508150	0.72kg	FBS-EN, ESTI ERIFLEX FleXbus, RoHS, CE				

#### **DETALII SUPLIMENTARE DESPRE PRODUS**

The thickness of the penetration seal has to be minimum 200mm, depending on the fire resistance classification (see Annex J-1 of the ETA) in order to obtain EI120 fire-resistance.

If 200mm is not possible, the FIB (intumescent wrap) needs to be used around the FleXbus Conductors and with 150mm width on both sides in order to reach EI120 fire resistance.

The width and height is referring to the maximum opening size of the penetration seal.

The total cross section of the installation (including insulation and conductor) must not be more than 60% of the opening size of the penetration seal.

The first support for the FleXbus Conductor has to be at a maximum 200mm measured from the surface of the penetration seal.

The FleXbus Foam Barrier FBS has to be used with the FFBD Foam Dispenser.

#### **AVERTIZARE**

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE