

nVent CADDY Speed Link Catenary Kit



CARACTERISTICI

Kit includes precut length of fuse-cut cable to avoid fraying, pre-assembled hook end fitting and tool-free locking device to save installation time

Fastens to the building structure by looping around and hooking to wire rope

Hook end-fitting easily attaches to eye nut

Spring latch helps provide secure connection

SPECIFICAȚII

Wire Rope Diameter: 6 mm

Finish: Electrogalvanized; Hot-Dip Galvanized

Table 1/2

Număr de catalog	Article Number	Material	Wire Rope Length	A	B	C
SLK6L10	196801	Steel, Zinc Alloy, Polypropylene	10m	75 mm	40 mm	15 mm
SLK6L15	196802	Steel, Zinc Alloy, Polypropylene	15m	75 mm	40 mm	15 mm
SLK6L20	196803	Steel, Zinc Alloy, Polypropylene	20m	75 mm	40 mm	15 mm

Număr de catalog	Article Number	Material	Wire Rope Length	A	B	C
SLK6L25	196804	Steel, Zinc Alloy, Polypropylene	25m	75 mm	40 mm	15 mm
SLK6L30	196805	Steel, Zinc Alloy, Polypropylene	30m	75 mm	40 mm	15 mm
SLK6L40	196806	Steel, Zinc Alloy, Polypropylene	40m	75 mm	40 mm	15 mm
SLK6L5	196800	Steel, Zinc Alloy, Polypropylene	5m	75 mm	40 mm	15 mm
SLK6L50	196807	Steel, Zinc Alloy, Polypropylene	50m	75 mm	40 mm	15 mm

Table 2/2

Număr de catalog	Article Number	Height (H)	Width (W)	Thickness (T)	Angle (a)
SLK6L10	196801	108 mm	41 mm	30 mm	60 ° Max
SLK6L15	196802	108 mm	41 mm	30 mm	60 ° Max
SLK6L20	196803	108 mm	41 mm	30 mm	60 ° Max
SLK6L25	196804	108 mm	41 mm	30 mm	60 ° Max
SLK6L30	196805	108 mm	41 mm	30 mm	60 ° Max
SLK6L40	196806	108 mm	41 mm	30 mm	60 ° Max
SLK6L5	196800	108 mm	41 mm	30 mm	60 ° Max
SLK6L50	196807	108 mm	41 mm	30 mm	60 ° Max

DETALII SUPLIMENTARE DESPRE PRODUS


Wire Rope Length is measured from the end of the wire rope to the hook side of the swage.

Static load 1 represents a point load in the center of the catenary installation. Static load 2 represents a two or three point distributed load on the catenary installation. Static load 3 represents a four or more point distributed load on the catenary installation.

Preload of the wire rope must be applied using Catenary Tensioning Tool.

Horizontal Installation		
Preload	1000 N	450 N
Static Load 1 (F1)	490 N	590 N
Static Load 2 (F2)	880 N	1080 N
Static Load 3 (F3)	980 N	1180 N
Vertical Installation		
Static Load 4 (F4)	4440 N	

DIAGRAMS



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Portofoliul nostru puternic de mărci:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

