

Arc Weldable Bond



CARACTERISTICI

19-strand concentric cable flash-welded to steel rod for a bonding connection to structural steel and to rebar

Economical alternative to exothermic welding when only a few connections need to be made and an arc welder is available on site

Rod is sized to match the ampacity of the cable for fault currents

SPECIFICAȚII

Table 1/1

Număr de catalog	Material	Conductor Size	Cable Length	Rod Size	Rod Length
EWB2Q344	Copper, Oțel	4/0 Stranded	1.2m	19.1mm	203mm

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Portofoliul nostru puternic de mărci:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE