

Cable to Ground Receptacle or Ground Plate, GF (To Ground Plate), DB Ground Plate, 95 mm² Concentric

Data Solutions

NUMĂR DE CATALOG

GFCY5DBG



nVent ERICO Cadweld graphite molds are designed and engineered for thousands of connection styles and conductor combinations.

CARACTERISTICI

Forms a permanent, low resistance connection

Provides a molecular bond

nVent ERICO Cadweld Exothermic Connections are rated with the same current capacity as the conductor

Portable installation equipment with no external source of power required

Installers can be easily trained to make nVent ERICO Cadweld Exothermic Connections

Connections can be visually inspected

ATRIBUTE PRODUS

Mold Family: GF (To Ground Plate) Mold family

Conductor Size: 95 mm² Concentric

Conductor Outer Diameter, Nominal: 12.83mm

Ground Plate/Grounding Receptacle: DB Ground Plate

Mold Split: Vertical

Split Crucible: No

Wear Plates: No

Mold Only: No

Welding Material: 115 or 115PLUSF20, Sold Separately

Handle Clamp: L160, Sold Separately

Frame: Not Required

Price Key: C

Ease of Use: Preferred

DETALII SUPLIMENTARE DESPRE PRODUS

For applications such as computer room, tunnel or other low-ventilation areas, specify a smokeless nVent ERICO Cadweld Exolon mold. Add an XL prefix to the standard mold part number when ordering (for example, a TAC2Q2Q becomes XLTAC2Q2Q). Similarly, nVent ERICO Cadweld Exolon welding material is also designated by the XL prefix (for example, 150 becomes XL150).

A gap between conductors may be required. See mold tag for more information.

XX-X-XX-XX-XX-L-M-W			
XX	Mold Family		
Χ	Price Key		
XX	Mold Family		
XX	Ground Rod Type		
XX	Conductor Code		
XX	Grounding Receptacle		
L*	Split Crucible	Crucible section is split on molds designed with horizontal opening for easier cleaning	
M*	Mold Only		
W*	Wear Plates	Reduce mechanical abrasion of molds at cable entry points	

* Empty if none

Empty in none			
XX-X-XX-L-M-W			
XX	Mold Family		
Χ	Price Key		
XX	Ground Plate/Grounding Receptacle		
XX	Conductor Code		
L*	Split Crucible	Crucible section is split on molds designed with horizontal opening for easier cleaning	
M*	Mold Only		
W*	Wear Plates	Reduce mechanical abrasion of molds at cable entry points	

^{*} Empty if none



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

CADDY HOFFMAN TRACHTE ERICO ILSCO SCHROFF