

nVent ERICO Cadweld One Shot for Rail, Cable to Ground Rod



nVent ERICO Cadweld applications for railway properties utilize the nVent ERICO Cadweld Plus F80 and the nVent ERICO Cadweld F80 welding material alloys. nVent ERICO Cadweld exothermically welded connections are engineered to provide a permanent, molecular bond that will not loosen or corrode, enabling connection of dissimilar materials. The connections are designed to perform for the life of the conductor and/or installation. The nVent ERICO Cadweld connection has a current carrying capacity equal to or greater than that of the conductor and will withstand repeated fault currents without failing during operation. Once completed, installers can clearly ensure quality by visually inspecting the new connection.

DIAGRAMS



CARACTERISTICI

For use with rail applications

Single use ceramic mold which eliminates the need for a graphite mold and handle clamp/frame (T320 flint igniter not included)

Produces a permanent connection that will not loosen or corrode

Fits plain copper-bonded, threaded copper-bonded, full-size galvanized and stainless steel ground rods

Supplied with F80 welding material

NEC® compliant

SPECIFICAȚII

Table 1/1

Număr de catalog	Mold Family	Ground Rod Diameter, Nominal	Ground Rod Diameter, Actual	Connection, Solid	Connection, Stranded
------------------	-------------	------------------------------	-----------------------------	-------------------	----------------------

SBGR1141G	GR (ONE SHOT)	1/2"	11.2 - 12.88 mm	10 mm ²	10 mm ²
SBGT1141L	GT (ONE SHOT)	1/2"	11.2 - 12.88 mm		16 mm ²
SBGT1161G	GT (ONE SHOT)	5/8"	11.2 - 12.88 mm	10 mm ²	10 mm ²
SBGT1161L	GT (ONE SHOT)	5/8"	11.2 - 12.88 mm		16 mm ²
SBGT1162G	GT (ONE SHOT)	5/8"	11.2 - 12.88 mm	70 mm ²	70 mm ²
SBNT1141G	NT (ONE SHOT)	1/2"	11.2 - 12.88 mm	10 mm ²	10 mm ²
SBGR1161G	GR (ONE SHOT)	5/8"	14.1 - 16.13 mm	10 mm ²	10 mm ²
SBGR1161L	GR (ONE SHOT)	5/8"	14.1 - 16.13 mm		16 mm ²
SBGR1162G	GR (ONE SHOT)	5/8"	14.1 - 16.13 mm	70 mm ²	70 mm ²
SBNT1161G	NT (ONE SHOT)	5/8"	14.1 - 16.13 mm	10 mm ²	10 mm ²
SBNT1161L	NT (ONE SHOT)	5/8"	14.1 - 16.13 mm		16 mm ²
SBNT1161V	NT (ONE SHOT)	5/8"	14.1 - 16.13 mm	50 mm ²	25 mm ² , 35 mm ²
SBNX1161G	NX (ONE SHOT)	5/8"	14.1 - 16.13 mm	10 mm ²	10 mm ²
SBNX1161L	NX (ONE SHOT)	5/8"	14.1 - 16.13 mm		16 mm ²
SBNX1161V	NX (ONE SHOT)	5/8"	14.1 - 16.13 mm	50 mm ²	25 mm ² , 35 mm ²
SBGR1161GPLUS	GR (ONE SHOT)	3/4"	14.0 - 16.1 mm	10 mm ² , 16 mm ²	10 mm ²
SBGR1161LPLUS	GR (ONE SHOT)	3/4"	14.0 - 16.1 mm		16 mm ²
SBGT1161GPLUS	GT (ONE SHOT)	3/4"	14.0 - 16.1 mm	10 mm ² , 16 mm ²	10 mm ²
SBGT1161LPLUS	GT (ONE SHOT)	3/4"	14.0 - 16.1 mm		16 mm ²

SBNT1161GPLUS	NT (ONE SHOT)	3/4"	14.0 - 16.1 mm	10 mm ² , 16 mm ²	10 mm ²
SBNT1161LPLUS	NT (ONE SHOT)	3/4"	14.0 - 16.1 mm		16 mm ²
SBNX1161GPLUS	NX (ONE SHOT)	3/4"	14.0 - 16.1 mm	10 mm ² , 16 mm ²	10 mm ²
SBNX1161LPLUS	NX (ONE SHOT)	3/4"	14.0 - 16.1 mm		16 mm ²
SBNX1161VPLUS	NX (ONE SHOT)	3/4"	14.0 - 16.1 mm	50 mm ²	25 mm ² , 35 mm ²
SBGR1181GPLUS	GR (ONE SHOT)	5/8"	17.0 - 19.43 mm	10 mm ² , 16 mm ²	10 mm ²
SBGR1181LPLUS	GR (ONE SHOT)	5/8"	17.0 - 19.43 mm		16 mm ²
SBGT1181GPLUS	GT (ONE SHOT)	5/8"	17.0 - 19.43 mm	10 mm ² , 16 mm ²	10 mm ²
SBGT1181LPLUS	GT (ONE SHOT)	5/8"	17.0 - 19.43 mm		16 mm ²
SBGT1181VPLUS	GT (ONE SHOT)	5/8"	17.0 - 19.43 mm	50 mm ²	25 mm ² , 35 mm ²
SBNT1181GPLUS	NT (ONE SHOT)	5/8"	17.0 - 19.43 mm	10 mm ² , 16 mm ²	10 mm ²
SBNT1181LPLUS	NT (ONE SHOT)	5/8"	17.0 - 19.43 mm		16 mm ²
SBNT1181VPLUS	NT (ONE SHOT)	5/8"	17.0 - 19.43 mm	50 mm ²	25 mm ² , 35 mm ²
SBNX1181GPLUS	NX (ONE SHOT)	5/8"	17.0 - 19.43 mm	10 mm ² , 16 mm ²	10 mm ²
SBNX1181LPLUS	NX (ONE SHOT)	5/8"	17.0 - 19.43 mm		16 mm ²
SBNX1181VPLUS	NX (ONE SHOT)	5/8"	17.0 - 19.43 mm	50 mm ²	25 mm ² , 35 mm ²
SBGR1181G	GR (ONE SHOT)	3/4"	17.1 - 19.43 mm	10 mm ²	10 mm ²
SBGR1181L	GR (ONE SHOT)	3/4"	17.1 - 19.43 mm		16 mm ²
SBGR1181V	GR (ONE SHOT)	3/4"	17.1 - 19.43 mm	50 mm ²	25 mm ² , 35 mm ²

SBGR1182C	GR (ONE SHOT)	3/4"	17.1 - 19.43 mm		50 mm ²
SBGR1182G	GR (ONE SHOT)	3/4"	17.1 - 19.43 mm	70 mm ²	70 mm ²
SBGR1182Q	GR (ONE SHOT)	3/4"	17.1 - 19.43 mm		95 mm ²
SBGT1181G	GT (ONE SHOT)	3/4"	17.1 - 19.43 mm	10 mm ²	10 mm ²
SBGT1181L	GT (ONE SHOT)	3/4"	17.1 - 19.43 mm		16 mm ²
SBGT1181V	GT (ONE SHOT)	3/4"	17.1 - 19.43 mm	50 mm ²	25 mm ² , 35 mm ²
SBGT1182C	GT (ONE SHOT)	3/4"	17.1 - 19.43 mm		50 mm ²
SBNT1181G	NT (ONE SHOT)	3/4"	17.1 - 19.43 mm	10 mm ²	10 mm ²
SBNT1181L	NT (ONE SHOT)	3/4"	17.1 - 19.43 mm		16 mm ²
SBNT1181V	NT (ONE SHOT)	3/4"	17.1 - 19.43 mm	50 mm ²	25 mm ² , 35 mm ²
SBNX1181G	NX (ONE SHOT)	3/4"	17.1 - 19.43 mm	10 mm ²	10 mm ²
SBNX1181L	NX (ONE SHOT)	3/4"	17.1 - 19.43 mm		16 mm ²
SBNX1181V	NX (ONE SHOT)	3/4"	17.1 - 19.43 mm	50 mm ²	25 mm ² , 35 mm ²

DETALII SUPLIMENTARE DESPRE PRODUS

A gap between conductors may be required. See mold tag for more information.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Portofoliul nostru puternic de mărci:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE