

RackChiller Rear Door Control Unit, Passive

Data Solutions



The Control Unit enriches the passive RackChiller Rear Door. It connects to the 4 built-in air temperature sensors and the motorized coolant valve 23130-607. This enables the cooler to control the coolant air flow based on a chilled (supply) air temperature setpoint. It provides advanced remote monitoring functionality and various setup features.

CERTIFICATIONS



CARACTERISTICI

Coolant flow control based on chilled (supply) air temperature setpoint. More control features with water control package 21130-608

Precise flow control against setpoint with parametric PID loop

Remote monitoring through built-in Web Server or BMS protocols (Modbus TCP, SNMP v2c)

Optional external display and keypad 21130-599

Languages: English, German, French

Power Supply: 90 - 260 VAC

SPECIFICAȚII

Table 1/1

Număr de catalog	Color
23130-594	Black Grey

DETALII SUPLIMENTARE DESPRE PRODUS

For trouble-free operation it is recommended to use the water connection set and the optional accessories.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE