


nVent ERIFLEX Flexbus HCBC Clamp



CERTIFICATIONS



CARACTERISTICI

Rigid design assures even contact pressure

Installs quickly and easily

Ideal for on-site modifications

Made with non-magnetic material stainless steel for high-current connections to prevent the formation of magnetic fields

Contains crimped self-locking nut for vibration resistance and easy installation

No drilling needed to fix the Flexbus Conductor on the transformer/power supply palm

Includes voltage detection connecting point

RoHS compliant

SPECIFICAȚII

Material: Stainless Steel 304 (EN 1.4301)

Table 1/2

Număr de catalog	Article Number	A	B	C	D	Thickness (T)
------------------	----------------	---	---	---	---	---------------

FLEXCLAMP63	508190	63 mm	123 mm	20 mm	43 mm	4 mm
FLEXCLAMP80	508191	80 mm	140 mm	20 mm	43 mm	4 mm
FLEXCLAMP160	508194	160 mm	220 mm	20 mm	43 mm	4 mm
FLEXCLAMP100	508192	100 mm	160 mm	20 mm	43 mm	4 mm
FLEXCLAMP120	508193	120 mm	180 mm	20 mm	43 mm	4 mm

Table 2/2

Număr de catalog	Article Number	Hole Size (HS)	Torque (TQ)	Unit Weight	Conductor Width
FLEXCLAMP63	508190	5.5 mm	100 N·m	0.53 kg	30 - 63 mm
FLEXCLAMP80	508191	5.5 mm	100 N·m	0.84 kg	70 - 80 mm
FLEXCLAMP160	508194	5.5 mm	100 N·m	1.32 kg	130 - 160 mm
FLEXCLAMP100	508192	5.5 mm	100 N·m	0.92 kg	90 - 100 mm
FLEXCLAMP120	508193	5.5 mm	100 N·m	1 kg	110 - 120 mm


DETALII SUPLIMENTARE DESPRE PRODUS

It is mandatory to use the HCBC Clamp associated with the HCBC Plate for proper Flexbus Conductor connection.

The minimum clearance distance is 14mm according to IEC 61439-1 with air pollution degree 3. If this distance cannot be respected, insulation material should be added between the metallic LV cover and the HCBC clamp. Flexbus IP2x Boots is also a solution.

If the Flexbus Conductors have a horizontal entry, an extender needs to be added between the power supply palm and HCBC Clamp and Plate.

DIAGRAMS



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE