

DT1 DIN Rail Surge Protection Class I+II 12.5 kA, 3+1 Mode



CERTIFICATIONS



CARACTERISTICI

Compact, yet high surge rated pluggable design, using minimum DIN rail width

External back-up fuse is not required up to 315 A (IEC only)

Retaining clip ensures enhanced vibration and shock resistance performance

Red/Green status indication and change-over contacts standard for remote monitoring


SPECIFICAȚII

Număr de catalog	DT130031R
Nominal System Voltage (Un)	240 V
Max Continuous Operating Voltage (Uc)	300 V L-N 305 V N-PE
Nominal Discharge Current (In), IEC, L-N	20kA 8/20 μs
Nominal Discharge Current (In), IEC, N-PE	50kA 8/20 μs
Max Discharge Current (Imax), IEC, L-N	50kA 8/20 μs

Număr de catalog	DT130031R
Max Discharge Current (I _{max}), IEC, N-PE	100kA 8/20 μs
Impulse Current (I _{imp}), L-N	12.5kA 10/350 μs
Impulse Current (I _{imp}), N-PE	50kA 10/350 μs
Voltage Protection Level (U _p), L-N	1400V
Voltage Protection Level (U _p), N-PE	1500V
Back-Up Fuse @ I _{sc} cr	250 A @ 50 kA 315 A @ 25 kA
Frequency	50 - 60 Hz
Response Time, L-N	25 ns Max
Response Time, N-PE	100 ns Max
Short Circuit Current Rating (I _{sc} cr)	25kA 50kA
Protection Modes	L-N N-PE
Temporary Over Voltage 120 min (U _t /mode), L-N	442 V Safe Fail
Temporary Over Voltage Withstand 200 ms (U _t), N-PE	1200V
Temporary Over Voltage Withstand 5 s (U _t), L-N	337V
Nominal Discharge Current (I _n), UL	20kA 8/20 μs
Replacement Module	DT1300M SGT150M
Voltage Protection Rating (VPR), L-N	900V
Voltage Protection Rating (VPR), N-PE	1500V
Short Circuit Current Rating (SCCR)	150kA
Technology	Thermal Disconnect
Connection, Solid	35 mm ² Max
Connection, Stranded	25 mm ² Max
Torque (TQ)	4.5 N·m
Humidity	5 - 95
Temperature	-35 to 85 °C
Enclosure Material	UL® 94V-0 Thermoplastic
Enclosure Rating	IP 20
Mounting	35 mm top hat DIN rail
Remote Contact Switching Capacity	1 A @ 250 VAC 1 A @ 125 VAC 0.5 A @ 48 VDC 0.5 A @ 24 VDC 0.5 A @ 12 VDC

Număr de catalog	DT130031R
Remote Contacts	Yes
Status Indication	Mechanical flag
Depth (D)	92mm
Height (H)	90 mm
Width (W)	72 mm
Unit Weight	0.68 kg
Certification Details	UL® 1449 Edition 5 Type 1CA
Complies With	EN 61643-11 Type 1, Type 2 IEC® 61643-11 Class I, Class II

DIAGRAMS



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Portofoliul nostru puternic de mărci:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE