

CS480 Base Bracket/Wall Flange



CS480 Base Bracket/Wall Flange allows for fixed positioning on a horizontal or vertical surface when rotation is not needed.

STANDARDE INDUSTRIALE

IEC 60529, IP66

CARACTERISTICI

Gasket and mounting hardware are included

Surface mounting fasteners are not provided

Assembled CS480 HMI Arm System has a max weight load of 89.6 lb. (40.7 kg)

SPECIFICAȚII

Table 1/1						
Număr de catalog	Height	Width	Depth	Material	Finish	Quick Ship
CCSS48BB	65mm	109mm	109mm	Stainless Steel 304	Lustruit	No

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE