

Grounding Busbar



Proper bonding is essential to create an equipotential plane between service grounds and equipment during fault and transient conditions. This equipotential plane provides a near-zero voltage differential, and serves to protect people and equipment during these events. The grounding busbar is the most popular bonding product in use today.

CERTIFICATIONS



DIAGRAMS



CARACTERISTICI

Provides a convenient, single-point grounding and bonding location

Conductors are welded to the bar using a nVent ERICO Cadweld exothermic connection or are mechanically fastened by using lugs

Custom bars can be designed and manufactured to customer specifications

SPECIFICAȚII

Busbar Configuration: Busbar, Insulators and Brackets

Material: Copper

Table 1/2

Număr de catalog	Hole Pattern	Mounting Hole Size	Length	Width	Thickness	Tin Plating
EGBA14212EET	EE	11.1mm	305mm	51 mm	6.4 mm	Yes
EGBA14424MM	MM	11.1mm	610mm	102 mm	6.4 mm	No
EGBA14215JJ	JJ	11.1mm	381mm	51 mm	6.4 mm	No
EGBA14220DGT	DG	11.1mm	508mm	51 mm	6.4 mm	Yes
EGBA14215EET	EE	11.1mm	381mm	51 mm	6.4 mm	Yes
EGBA14224EET	EE	11.1mm	610mm	51 mm	6.4 mm	Yes
EGBA14206EET	EE	11.1mm	152mm	51 mm	6.4 mm	Yes
EGBA14224GGT	GG	11.1mm	610mm	51 mm	6.4 mm	Yes
EGBA14216HH	HH	11.1mm	406mm	51 mm	6.4 mm	No

Table 2/2

Număr de catalog	Pigtail Included
EGBA14212EET	No
EGBA14424MM	No
EGBA14215JJ	No
EGBA14220DGT	No
EGBA14215EET	No
EGBA14224EET	No
EGBA14206EET	No

Număr de catalog	Pigtail Included
EGBA14224GGT	No
EGBA14216HH	No

DETALII SUPLIMENTARE DESPRE PRODUS

Diagrams are representative of the hole pattern. The number of holes is dependent on the length of the grounding busbar.

Additional configurations are available by special order. Note special orders may incur additional lead time.

EGB-A-14-4-12-CC-T-1T-K		
EGB	ERICO Grounding Busbar Designation	
A	Configuration	A: Busbar, Insulators and Brackets B: Busbar and Brackets C: Busbar Only D: Busbar and Insulators
14	Thickness (")	14: 1/4" · 38: 3/8" · 12: 1/2"
4	Width (")	
12	Length (")	Rounded to the nearest inch, 144" max
CC	Hole Pattern	Diagrams are representative of the hole pattern. The number of holes is dependent on the length of the grounding busbar.
T*	Tin Plating	
1T*	ERICO Cable Code	1K: #4 Sol Tin · 1T: #2 Sol Tin 2C: 1/0 · 2G: 2/0 · 2L: 3/0 · 2Q: 4/0 2V: 250 kcmil · 3D: 350 kcmil · 3Q: 500 kcmil · 4L: 750 kcmil
K*	Pigtail Length (")	A:1 · B:2 · C:3 · D:4 · E:5 · F:6 · G:7 · H:8 · J:9 · K:10 · L:12 · M:14 · N:16 P:18 · Q:20 · R:22 · S:24 · T:26 · U:28 · V:30 · W:32 · X:34 · Y:36 · Z:38

* Empty if none

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Portofoliul nostru puternic de mărci:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE