

Zonex Stainless Steel Terminal Box, EXE-SB



The stainless steel terminal box enclosure range, EXE, with ATEX and IECEx certifications, is available off the shelf in five different sizes that accommodate the majority of common applications. ZONEX enclosures deliver a robust solution for termination and junction enclosure applications in potentially hazardous locations, including petroleum and chemical processing, water treatment processing, pharmaceutical processing, and grain processing.; ZONEX enclosures are designed and certified to meet ATEX Directive 2014/34/EU as well as IECEx standards for increased safety in housing electrical components in Zone 1 and Zone 2 applications.

STANDARDE INDUSTRIALE

cULus_UL Listed

ATEX

CE

DoC NEC Class 1 Div 2

IECEx

CARATTERISTICI

ATEX- and IECEx-certified enclosure

Time and cost savings in the end-use investigation process of the final assembly

Certification of final assembly is easier if enclosures are certified

Body: M6 brass internal/external bonding provision; full-width welded wall-mounting brackets on top and bottom. Internal weld studs for panel or DIN rail mounting brackets

Cover: One piece continuous seal polyurethane gasket, operating range -40 to +70 °C; type 316L stainless steel cover screws; M6 inner grounding stud; optional silicone gasket with operating range -55 to +180 °C

Approvals: ATEX Directive 2014/34/EU. ATEX: Sira 09ATEX3224U; 2813 Ex II 2 G D; Ex e IIC Gb; Ex tb IIIC Db IP 66; EN 60079-0; EN 60079-7; EN 60079-31. IECEx: IECEx SIR 09.0099U; Ex eb IIC Gb; Ex tb IIIC Db IP 66; IEC 60079-0; IEC 60079-7; IEC 60079-31

Delivery: Enclosure with cover, cover screws, mounting plate and mounting accessories

SPECIFICAȚII

Thickness (T):	2.5mm
Finish:	Brushed 320
Material:	Oțel Inoxidabil 316L


Table 1/1

Număr de catalog	Height (H)	Width (W)	Depth (D)	Panel Size	Quick Ship
EXE151510SS6E	152mm	152mm	102mm	135 x 135mm	No
EXE252513SS6E	254mm	254mm	127mm	237 x 237mm	No
EXE221513SS6E	216mm	146mm	127mm	199 x 129mm	No
EXE181810SS6E	178mm	178mm	102mm	161 x 161mm	No
EXE101008SS6E	102mm	102mm	76mm	85 x 85mm	No

DETALII SUPLIMENTARE DESPRE PRODUS

Note: nVent HOFFMAN ATEX Ex e enclosures are not intended for use in explosion-proof or flame-proof applications. NEMA 4X enclosure (as a component) is suitable and complies with NEC Class I, Division 2, Groups A, B, C, D assemblies when properly evaluated and using terminal blocks and/or approved Class I, Division 1 or 2 (no arcs, sparks or hot surfaces) devices installed within the enclosure in accordance with NEC/CEC requirements (reference NEC 2011 Article 501.10(B)(4) and NEC 2011 Handbook).

DIAGRAMS



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE