

Front Panel, Front Anodized, Rear Conductive, Unshielded

Front panel, unshielded, front anodized and rear conductive.



CERTIFICATIONS



CARACTERISTICI

Partial width front panel, Al, 2.5 mm

Al, front anodized, conductive

SPECIFICAȚII

Depth (D):	2.5mm
Material:	Aluminiu
Finish:	Anodized; Passivated
Accessory Type:	Front panel
Product Type:	Front Panel
Type:	Front Panel without Handle

Table 1/2

Număr de catalog	Rack Height	Package Quantity	Mounting	Front Finish	Rear Finish	Treated Edges
30847-471	3U	1	Screw-on Front	Anodized	Conductive	No

Număr de catalog	Rack Height	Package Quantity	Mounting	Front Finish	Rear Finish	Treated Edges
30838-043	3U	1	Screw-on Front	Anodized	Conductive	No
30838-044	3U	1	Screw-on Front	Anodized	Conductive	No
30838-045	3U	1	Screw-on Front	Anodized	Conductive	No
30838-046	3U	1	Screw-on Front	Anodized	Conductive	No
30838-047	3U	1	Screw-on Front	Anodized	Conductive	No
30838-124	6U	1	Screw-on Front	Anodized	Conductive	No
30838-049	3U	1	Screw-on Front	Anodized	Conductive	No
30838-125	6U	1	Screw-on Front	Anodized	Conductive	No
30838-051	3U	1	Screw-on Front	Anodized	Conductive	No
30838-126	6U	1	Screw-on Front	Anodized	Conductive	No
30847-476	4U	1	Screw-on Front	Anodized	Conductive	No
30838-053	3U	1	Screw-on Front	Anodized	Conductive	No
30838-127	6U	1	Screw-on Front	Anodized	Conductive	No
30838-055	3U	1	Screw-on Front	Anodized	Conductive	No
30838-123	3U	1	Screw-on Front	Anodized	Conductive	No
30838-128	6U	1	Screw-on Front	Anodized	Conductive	No
30847-458	2U	1	Screw-on Front	Anodized	Conductive	No
30838-130	6U	1	Screw-on Front	Anodized	Conductive	No

Număr de catalog	Rack Height	Package Quantity	Mounting	Front Finish	Rear Finish	Treated Edges
30838-060	3U	1	Screw-on Front	Anodized	Conductive	No
30838-132	6U	1	Screw-on Front	Anodized	Conductive	No
30847-480	9U	1	Screw-on Front	Anodized	Conductive	No
30847-459	2U	1	Screw-on Front	Anodized	Conductive	No
30838-067	3U	1	Screw-on Front	Anodized	Conductive	No
30838-134	6U	1	Screw-on Front	Anodized	Conductive	No
30838-136	6U	1	Screw-on Front	Anodized	Conductive	No
30847-462	4U	1	Screw-on Front	Anodized	Conductive	No
30847-484	9U	1	Screw-on Front	Anodized	Conductive	No
30847-460	2U	1	Screw-on Front	Anodized	Conductive	No
30838-081	3U	1	Screw-on Front	Anodized	Conductive	No
30838-141	6U	1	Screw-on Front	Anodized	Conductive	No
30847-461	2U	1	Screw-on Front	Anodized	Conductive	No
30838-148	6U	1	Screw-on Front	Anodized	Conductive	No
30847-463	4U	1	Screw-on Front	Anodized	Conductive	No
30847-466	5U	1	Screw-on Front	Anodized	Conductive	No
30838-102	3U	1	Screw-on Front	Anodized	Conductive	No
30847-467	5U	1	Screw-on Front	Anodized	Conductive	No

Număr de catalog	Rack Height	Package Quantity	Mounting	Front Finish	Rear Finish	Treated Edges
30847-464	4U	1	Screw-on Front	Anodized	Conductive	No
30838-162	6U	1	Screw-on Front	Anodized	Conductive	No
30847-468	5U	1	Screw-on Front	Anodized	Conductive	No
30847-465	4U	1	Screw-on Front	Anodized	Conductive	No
30838-183	6U	1	Screw-on Front	Anodized	Conductive	No
30847-469	5U	1	Screw-on Front	Anodized	Conductive	No
30838-204	6U	1	Screw-on Front	Anodized	Conductive	No
30847-470	3U	1	Screw-on Front	Anodized	Conductive	No
30847-482	9U	1	Screw-on Front	Anodized	Conductive	No
30847-556	9U	1	Screw-on Front	Anodized	Conductive	No

Table 2/2

Număr de catalog	Complies With	EMC Shielding	Height (H)	Width (W)	Certifications	Quick Ship
30847-471	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	14.9mm	RoHS	No
30838-043	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	20mm	RoHS	No
30838-044	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	25mm	RoHS	No
30838-045	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	30.1mm	RoHS	No
30838-046	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	35.2mm	RoHS	No

Număr de catalog	Complies With	EMC Shielding	Height (H)	Width (W)	Certifications	Quick Ship
30838-047	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	40.3mm	RoHS	No
30838-124	IEC 60297-3-101, IEEE 1101.1/10	No	261.8mm	20mm	RoHS	No
30838-049	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	50.5mm	RoHS	No
30838-125	IEC 60297-3-101, IEEE 1101.1/10	No	261.8mm	25mm	RoHS	No
30838-051	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	60.6mm	RoHS	No
30838-126	IEC 60297-3-101, IEEE 1101.1/10	No	261.8mm	30.1mm	RoHS	No
30847-476	IEC 60297-3-101, IEEE 1101.1/10	No	395.1mm	20mm	RoHS	No
30838-053	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	70.8mm	RoHS	No
30838-127	IEC 60297-3-101, IEEE 1101.1/10	No	261.8mm	35.2mm	RoHS	No
30838-055	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	80.9mm	RoHS	No
30838-123	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	426.4mm	RoHS	No
30838-128	IEC 60297-3-101, IEEE 1101.1/10	No	261.8mm	40.3mm	RoHS	No
30847-458	IEC 60297-3-101, IEEE 1101.1/10	No	84mm	141.9mm		No
30838-130	IEC 60297-3-101, IEEE 1101.1/10	No	261.8mm	50.5mm	RoHS	No


Număr de catalog	Complies With	EMC Shielding	Height (H)	Width (W)	Certifications	Quick Ship
30838-060	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	106.3mm	RoHS	No
30838-132	IEC 60297-3-101, IEEE 1101.1/10	No	261.8mm	60.6mm	RoHS	No
30847-480	IEC 60297-3-101, IEEE 1101.1/10	No	395.1mm	40.3mm	RoHS	No
30847-459	IEC 60297-3-101, IEEE 1101.1/10	No	84mm	213mm		No
30838-067	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	141.9mm	RoHS	No
30838-134	IEC 60297-3-101, IEEE 1101.1/10	No	261.8mm	70.8mm	RoHS	No
30838-136	IEC 60297-3-101, IEEE 1101.1/10	No	261.8mm	80.9mm	RoHS	No
30847-462	IEC 60297-3-101, IEEE 1101.1/10	No	172.9mm	141.9mm		No
30847-484	IEC 60297-3-101, IEEE 1101.1/10	No	395.1mm	60.6mm	RoHS	No
30847-460	IEC 60297-3-101, IEEE 1101.1/10	No	84mm	319.7mm		No
30838-081	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	213mm	RoHS	No
30838-141	IEC 60297-3-101, IEEE 1101.1/10	No	261.8mm	106.3mm	RoHS	No
30847-461	IEC 60297-3-101, IEEE 1101.1/10	No	84mm	426.4mm	RoHS	No
30838-148	IEC 60297-3-101, IEEE 1101.1/10	No	261.8mm	141.9mm	RoHS	No

Număr de catalog	Complies With	EMC Shielding	Height (H)	Width (W)	Certifications	Quick Ship
30847-463	IEC 60297-3-101, IEEE 1101.1/10	No	172.9mm	213mm	RoHS	No
30847-466	IEC 60297-3-101, IEEE 1101.1/10	No	217.4mm	141.9mm		No
30838-102	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	319.7mm	RoHS	No
30847-467	IEC 60297-3-101, IEEE 1101.1/10	No	217.4mm	213mm		No
30847-464	IEC 60297-3-101, IEEE 1101.1/10	No	172.9mm	319.7mm	RoHS	No
30838-162	IEC 60297-3-101, IEEE 1101.1/10	No	261.8mm	213mm	RoHS	No
30847-468	IEC 60297-3-101, IEEE 1101.1/10	No	217.4mm	319.7mm		No
30847-465	IEC 60297-3-101, IEEE 1101.1/10	No	172.9mm	426.4mm	RoHS	No
30838-183	IEC 60297-3-101, IEEE 1101.1/10	No	261.8mm	319.7mm	RoHS	No
30847-469	IEC 60297-3-101, IEEE 1101.1/10	No	217.4mm	426.4mm		No
30838-204	IEC 60297-3-101, IEEE 1101.1/10	No	261.8mm	426.4mm	RoHS	No
30847-470	IEC 60297-3-101, IEEE 1101.1/10	No	128.4mm	9.8mm	RoHS	No
30847-482	IEC 60297-3-101, IEEE 1101.1/10	No	395.1mm	50.5mm	RoHS	No
30847-556	IEC 60297-3-101, IEEE 1101.1/10	No	395.1mm	426.4mm	RoHS	No

DETALII SUPLIMENTARE DESPRE PRODUS

Please order fixing material (sleeves, collar screws) separately.

DIAGRAMS



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE