

19" Fan Unit, 1 U, Remote Control and Monitoring

Power Utilities

Fan Unit with ModBus interface for installation into a 1 U space within the Cabinet

CARACTERISTICI

Fan speed temperature controlled

ModBus Interface for Remote Monitoring and Control

Temperature threshold for the fan control adjustable on the front panel

Signaling of fan failure and over temperature by 2 LEDs and potential-free relay outputs

Integrated power supply with wide range input (100 V – 240 V)

Less than 1 U (42 mm) to enable mounting on sliding guide rails or drawer

2 NTC temperature sensors with Cables included

SPECIFICAȚII

Table 1/2

Număr de catalog	Input Voltage AC	Airflow	Noise Level	Power	Max Static Pressure	Ambient Temperature
10713-554	100 – 240 V	1089 m³/h	59.5 dB(A)	97 W	78 Pa	–10 to 70 °C

Table 2/2

Număr de catalog	Lifespan, L10 @ 40 C
10713-554	99558 h

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte

și/sau poate anula garanția dvs.



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE