

# nVent CADDY Speed Link SLK with Hook



## CERTIFICATIONS



## FEATURES

Complete system includes wire, locking device and pre-assembled hook end fitting

Hooks to a wide range of nVent CADDY fasteners

Fastens to the building structure or hanging services by looping around and hooking to wire rope

Easy to remove for applications requiring maintenance

Spring latch helps provide secure connection

Insert cable through hole and use bottom side of hook as an end stop

Also available in Y-hook configuration

## SPECIFICATIONS

**Static Load Safety Factor:** 5:1

**Finish:** Electrogalvanized

**Complies With:** SMACNA HVAC-DCS

Table 1/3

Catalog Number	Article Number	Material	Wire Rope Diameter	Wire Rope Length	A	B
----------------	----------------	----------	--------------------	------------------	---	---

SLK15L1	196508	Steel, Polypropylene, Zinc Alloy	1.5 mm	1m	48 mm	18 mm
SLK15L10	196513	Steel, Polypropylene, Zinc Alloy	1.5 mm	10m	48 mm	18 mm
SLK15L2	196509	Steel, Polypropylene, Zinc Alloy	1.5 mm	2m	48 mm	18 mm
SLK15L2R2	196614	Steel, Polypropylene, Zinc Alloy	1.5 mm	2m	48 mm	18 mm
SLK15L3	196510	Steel, Polypropylene, Zinc Alloy	1.5 mm	3m	48 mm	18 mm
SLK15L3R2	196615	Steel, Polypropylene, Zinc Alloy	1.5 mm	3m	48 mm	18 mm
SLK15L5	196511	Steel, Polypropylene, Zinc Alloy	1.5 mm	5m	48 mm	18 mm
SLK2L1	196537	Steel, Polypropylene, Zinc Alloy	2 mm	1m	57 mm	22 mm
SLK2L10	196542	Steel, Polypropylene, Zinc Alloy	2 mm	10m	57 mm	22 mm
SLK2L2	196538	Steel, Polypropylene, Zinc Alloy	2 mm	2m	57 mm	22 mm
SLK2L2R2	196619	Steel, Polypropylene, Zinc Alloy	2 mm	2m	57 mm	22 mm
SLK2L3	196539	Steel, Polypropylene, Zinc Alloy	2 mm	3m	57 mm	22 mm
SLK2L3R2	196620	Steel, Polypropylene, Zinc Alloy	2 mm	3m	57 mm	22 mm
SLK2L5	196540	Steel, Polypropylene, Zinc Alloy	2 mm	5m	57 mm	22 mm
SLK3L1	196700	Steel, Polypropylene, Zinc Alloy	3 mm	1m	57.6 mm	23.2 mm

SLK3L10	196705	Steel, Polypropylene, Zinc Alloy	3 mm	10m	57.6 mm	23.2 mm
SLK3L2	196701	Steel, Polypropylene, Zinc Alloy	3 mm	2m	57.6 mm	23.2 mm
SLK3L3	196702	Steel, Polypropylene, Zinc Alloy	3 mm	3m	57.6 mm	23.2 mm
SLK3L3R2	196625	Steel, Polypropylene, Zinc Alloy	3 mm	3m	57.6 mm	23.2 mm
SLK3L5	196703	Steel, Polypropylene, Zinc Alloy	3 mm	5m	57.6 mm	23.2 mm
SLK3L5R2	196626	Steel, Polypropylene, Zinc Alloy	3 mm	5m	57.6 mm	23.2 mm

Table 2/3

Catalog Number	Article Number	C	Height (H)	Width (W)	Thickness (T)	Angle (a)
SLK15L1	196508	4.5 mm	55 mm	19 mm	12.5 mm	90 ° Max
SLK15L10	196513	4.5 mm	55 mm	19 mm	12.5 mm	90 ° Max
SLK15L2	196509	4.5 mm	55 mm	19 mm	12.5 mm	90 ° Max
SLK15L2R2	196614	4.5 mm	55 mm	19 mm	12.5 mm	90 ° Max
SLK15L3	196510	4.5 mm	55 mm	19 mm	12.5 mm	90 ° Max
SLK15L3R2	196615	4.5 mm	55 mm	19 mm	12.5 mm	90 ° Max
SLK15L5	196511	4.5 mm	55 mm	19 mm	12.5 mm	90 ° Max
SLK2L1	196537	5.5 mm	55 mm	19 mm	12.5 mm	90 ° Max
SLK2L10	196542	5.5 mm	55 mm	19 mm	12.5 mm	90 ° Max
SLK2L2	196538	5.5 mm	55 mm	19 mm	12.5 mm	90 ° Max


CatalogNumber	Article Number	C	Height (H)	Width (W)	Thickness (T)	Angle (a)
SLK2L2R2	196619	5.5 mm	55 mm	19 mm	12.5 mm	90 ° Max
SLK2L3	196539	5.5 mm	55 mm	19 mm	12.5 mm	90 ° Max
SLK2L3R2	196620	5.5 mm	55 mm	19 mm	12.5 mm	90 ° Max
SLK2L5	196540	5.5 mm	55 mm	19 mm	12.5 mm	90 ° Max
SLK3L1	196700	6.1 mm	62 mm	24 mm	16 mm	90 ° Max
SLK3L10	196705	6.1 mm	62 mm	24 mm	16 mm	90 ° Max
SLK3L2	196701	6.1 mm	62 mm	24 mm	16 mm	90 ° Max
SLK3L3	196702	6.1 mm	62 mm	24 mm	16 mm	90 ° Max
SLK3L3R2	196625	6.1 mm	62 mm	24 mm	16 mm	90 ° Max
SLK3L5	196703	6.1 mm	62 mm	24 mm	16 mm	90 ° Max
SLK3L5R2	196626	6.1 mm	62 mm	24 mm	16 mm	90 ° Max

Table 3/3

Catalog Number	Article Number	Static Load	Certifications
SLK15L1	196508	195N	UL, cUL, SMACNA
SLK15L10	196513	195N	SMACNA, UL, cUL
SLK15L2	196509	195N	SMACNA, UL, cUL
SLK15L2R2	196614	195N	SMACNA, UL, cUL
SLK15L3	196510	195N	UL, cUL, SMACNA
SLK15L3R2	196615	195N	UL, cUL, SMACNA

Catalog Number	Article Number	Static Load	Certifications
SLK15L5	196511	195N	SMACNA, UL, cUL
SLK2L1	196537	440N	SMACNA, UL, cUL
SLK2L10	196542	440N	SMACNA, UL, cUL
SLK2L2	196538	440N	UL, cUL, SMACNA
SLK2L2R2	196619	440N	UL, cUL, SMACNA
SLK2L3	196539	440N	SMACNA, UL, cUL
SLK2L3R2	196620	440N	SMACNA, UL, cUL
SLK2L5	196540	440N	UL, cUL, SMACNA
SLK3L1	196700	890N	SMACNA
SLK3L10	196705	890N	SMACNA
SLK3L2	196701	890N	SMACNA
SLK3L3	196702	890N	SMACNA
SLK3L3R2	196625	890N	SMACNA
SLK3L5	196703	890N	SMACNA
SLK3L5R2	196626	890N	SMACNA

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

