


Передняя панель, неэкранированная, с вырезами для коаксиальных разъемов

CATALOG NUMBER

30118-355



Алюминий, 2,5 мм, анодированная с лицевой стороны, проводящая, неэкранированная версия.

CERTIFICATIONS



FEATURES

алюминий, 2,5 мм, лицевая поверхность анодированная, токопроводящая

3 U, 4 HP

PRODUCT ATTRIBUTES

Product Type: Передняя панель

Type: Front Panel without Handle

Аксессуар Тип: Передняя панель

Mounting: Screw-on Front

EMC Shielding: Нет

Material: Алюминий

Front Finish: Anodized

Rear Finish: Conductive

Treated Edges: Нет

Rack Height: 3U

Высота мм (H): 128.4mm

Rack Width: 4HP

Ширина мм (W): 19.98mm

Глубина мм (D): 2.5mm

Complies With: IEC 60297-3-101; IEEE 1101.1/10

Package Quantity: 1


Finish: Anodized; Passivated

Net Weight: 0.013kg

ADDITIONAL PRODUCT DETAILS

Крепежный материал (втулки, винты с проточкой) заказывается отдельно.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE