


# Кронштейн печатной платы для крепления передней панели/печатной платы, оцинкованный

## CATALOG NUMBER

60807-181



Опорные держатели для печатных плат позволяют крепить печатную плату к передней панели. Предлагается в различных материалах.

## CERTIFICATIONS



## FEATURES

Для крепления печатных плат на передней панели

PRODUCT ATTRIBUTES

Material: Zinc Alloy
Package Quantity: 1
Глубина мм: 8.6mm
Высота мм: 11.1mm
Product Type: Bracket
Type: PCB Bracket
Ширина мм: 10.2mm
Works With: Передние панели
Thread Size: M2.5
Thread Type: Metric

ADDITIONAL PRODUCT DETAILS

Поставка исключительно в размере товарной партии. Цена указана за отдельную единицу.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

<b>North America</b> All locations +1.763.422.2661 Chat with us: <a href="http://nvent.com/schroff">nvent.com/schroff</a>	<b>Europe</b> Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: <a href="http://nvent.com/schroff">nvent.com/schroff</a>	<b>Asia</b> Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: <a href="http://nvent.com/schroff">nvent.com/schroff</a>	<b>Middle East &amp; India</b> Dubai, United Arab Emirates +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: <a href="http://nvent.com/schroff">nvent.com/schroff</a>
---	---	---	---



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE