

# Enlogic Input Metered PDU EN1 Series

## Data Solutions



The Advantage Series Input Metered PDU family offers energy metering with advanced power and environmental monitoring options. Comprehensive monitoring at both the input phase and circuit breaker levels offers advanced alerts of potential overloads. Billing-grade metering provides accurate power consumption data for energy use optimization. The hot-swappable network management controller features Gigabit and redundant ethernet communication with advanced support for external environmental sensors and rack security access solutions.

### FEATURES

Black Powder Coated Chassis

IEC 62368 listed. RoHS, and REACH compliant. See drawing for additional information.

UL 2900-1 certified for safety software cybersecurity for network-connectable products.

Dual network connectivity ports: 1x Gigabit Ethernet (10/100/1000 Mbps) and 1x (10/100 Mbps) connection/IP address

Ethernet cascading up to 64 PDUs

Each PDU can provide DC power sufficient to power network management electronics

Dual Ethernet ports for redundant network communications

Remote connectivity through HTTP(s), IPv4 and IPv6, SSH, Virtual Serial, SNMP (v1, v2c, v3), JSON-RPC, LDAP(S)

Data efficient REACT framework with native mobile device support

Tool-less hot swappable Network Management Card (NMC) with Cortex A-5 for microprocessing and memory that can be installed both upright and upside down for top or bottom power inputs

The border color of the NMC display is user programmable for power source identification by PDU

The NMC supports up to 10 digital sensors for environmental and/or electronic lock monitoring

Display languages include English, Spanish, German, French, Italian, Korean, Japanese, and Chinese (simplified)

### SPECIFICATIONS

Table 1/5

| Catalog Number | Product Family | Type | Product Type | Socket Type | Socket Quantity | Color |
|----------------|----------------|------|--------------|-------------|-----------------|-------|
|----------------|----------------|------|--------------|-------------|-----------------|-------|

|        |         |                      |                       |                                    |    |        |
|--------|---------|----------------------|-----------------------|------------------------------------|----|--------|
| EN1361 | Enlogic | Интеллектуальные PDU | Панели электропитания | (9) C13/C15/C19/C21                | 9  | Черный |
| EN19HD | Enlogic | Интеллектуальные PDU | Панели электропитания | (18) C13/C15, (18) C13/C15/C19/C21 | 36 | Черный |

Table 2/5

| Catalog Number | Switched Outlets | Cable Length | Power Rating                                 | Circuit Breaker       | Circuit Breaker Quantity | Phase |
|----------------|------------------|--------------|----------------------------------------------|-----------------------|--------------------------|-------|
| EN1361         | Нет              | 3000mm       | 3.7 kVA                                      | No Circuit Breaker    | 0                        | 1 PH  |
| EN19HD         | Нет              | 1800mm       | 57.6 kVA North America, 69 kVA International | 20 A, 1-pole, Hy-MagA | 18                       |       |

Table 3/5

| Catalog Number | Nominal Power Output | Nominal Voltage | Number of Output Voltages | On/Off Switch Included | Output Voltage | Amperage (Derated Amperage)                     |
|----------------|----------------------|-----------------|---------------------------|------------------------|----------------|-------------------------------------------------|
| EN1361         | 230VAC               | 230V            | 12                        | Нет                    | 230VAC         | 16 A                                            |
| EN19HD         | 230VAC               | 415V            | 36                        | Нет                    | 208 – 230VAC   | 100 A (80 A) North America, 100 A International |

Table 4/5

| Catalog Number | Plug Type                | Rack Units | Removable Input Cable | Metering Type | Material | Finish        |
|----------------|--------------------------|------------|-----------------------|---------------|----------|---------------|
| EN1361         | IEC 60309 316P6 (IP44)   | 1U         | Да                    | Input         | Сталь    | Powder Coated |
| EN19HD         | IEC 60309 5125P6W (IP67) | 0U         | Нет                   | Input         | Сталь    | Powder Coated |

Table 5/5

| Catalog Number | Высота мм | Ширина мм | Глубина мм | Weight | Package Quantity | Input Cable Length |
|----------------|-----------|-----------|------------|--------|------------------|--------------------|
| EN1361         | 43mm      | 444mm     | 269mm      | 4.4kg  | 1                | 3m                 |
| EN19HD         | 1750mm    | 59mm      | 87mm       |        | 1                | 1.8m               |

## ADDITIONAL PRODUCT DETAILS

---

Warranty : nVent Enlogic branded equipment provided shall be free from manufacturing defects for a period of five (5) years from the invoice date to the original purchaser.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**