

# Intelligent PDU, EN1xxx, 400 VAC, 3-PH

## Data Solutions



Modular, compact intelligent PDU with inlet metering. Ultra-Low Profile Design

### FEATURES

Enlogic EN1xxx Intelligent Power Distribution Units monitors input power of the entire PDU, provides billing grade unit level monitoring

High Visibility Data Display and Interactive Graphic Display

Measure circuit breaker loads across redundant feeds to avoid accidental downtime

Enables smart load balancing for power efficiency and maximized capacity utilization

Gigabit Ethernet Interface and redundant Ethernet (10/100)

iPDU DC power redundancy solution for up to 64 PDU's

Toolless Hot-Swap Controller

Input voltage 400 VAC, 3-phase

C13, C19 outlets

### SPECIFICATIONS

Table 1/6

| Catalog Number | Product Family | Type                 | Product Type          | Socket Type                        | Socket Quantity | Color  |
|----------------|----------------|----------------------|-----------------------|------------------------------------|-----------------|--------|
| EN1403         | Enlogic        | Интеллектуальные PDU | Панели электропитания | (36) C13, (6) C19                  | 42              | Черный |
| EN1450         | Enlogic        | Интеллектуальные PDU | Панели электропитания | (21) C13/C15, (21) C13/C15/C19/C21 | 42              | Черный |
| EN1402         | Enlogic        | Интеллектуальные PDU | Панели электропитания | (24) C13, (6) C19                  | 30              | Черный |

| CatalogNumber | Product Family | Type                 | Product Type          | Socket Type                                        | SocketQuantity | Color  |
|---------------|----------------|----------------------|-----------------------|----------------------------------------------------|----------------|--------|
| EN1811        | Enlogic        | Интеллектуальные PDU | Панели электропитания | (30) C13, (12) C19                                 | 42             | Черный |
| EN1850        | Enlogic        | Интеллектуальные PDU | Панели электропитания | (24) C13/C15, (24) C13/C15/C19/C21                 | 48             | Черный |
| EN1880        | Enlogic        | Интеллектуальные PDU | Панели электропитания | (21) Locking C13/C15, (21) Locking C13/C15/C19/C21 | 42             | Черный |
| EN1950        | Enlogic        | Интеллектуальные PDU | Панели электропитания | (21) C13/C15, (21) C13/C15/C19/C21                 | 42             | Черный |
| EN1980        | Enlogic        | Интеллектуальные PDU | Панели электропитания | (18) Locking C13/C15, (18) Locking C13/C15/C19/C21 | 36             | Черный |
| EN1808        | Enlogic        | Интеллектуальные PDU | Панели электропитания | (12) C13, (12) C19                                 | 24             | Черный |
| EN1809        | Enlogic        | Интеллектуальные PDU | Панели электропитания | (18) C13, (6) C19                                  | 24             | Черный |
| EN1812        | Enlogic        | Интеллектуальные PDU | Панели электропитания | (36) C13, (12) C19                                 | 48             | Черный |

Table 2/6

| Catalog Number | Circuit Breaker      | Switched Outlets | Circuit Breaker Quantity | Power Rating                                   | Input Cable Length | Input Cable Location |
|----------------|----------------------|------------------|--------------------------|------------------------------------------------|--------------------|----------------------|
| EN1403         | No Circuit Breaker   | Нет              | 0                        | 11.0 kVA                                       | 3m                 | Top Feed             |
| EN1450         | No Circuit Breaker   | Нет              | 0                        | 11.5 kVA North America, 11.0 kVA International | 1.8m               | Top Feed             |
| EN1402         | 16 A, 1-pole, Hy-Mag | Нет              | 0                        |                                                |                    | Top Feed             |
| EN1811         | 16 A, 1-pole, Hy-Mag | Нет              | 6                        | 22.0 kVA                                       | 3m                 | Top Feed             |

| CatalogNumber | Circuit Breaker      | Switched Outlets | Circuit Breaker Quantity | Power Rating                                   | Input Cable Length | Input Cable Location |
|---------------|----------------------|------------------|--------------------------|------------------------------------------------|--------------------|----------------------|
| EN1850        | 20 A, 1-pole, Hy-Mag | HeT              | 6                        | 17.3 kVA North America, 22.1 kVA International | 1.8m               | Top Feed             |
| EN1880        | 20 A, 1-pole, Hy-Mag | HeT              | 6                        | 17.3 kVA North America, 22.1 kVA International | 1.8m               | Top Feed             |
| EN1950        | 20 A, 1-pole, Hy-Mag | HeT              | 12                       | 34.6 kVA North America, 43.5 kVA International | 1.8m               | Top Feed             |
| EN1980        | 20 A, 1-pole, Hy-Mag | HeT              | 12                       | 34.6 kVA North America, 43.5 kVA International | 1.8m               | Top Feed             |
| EN1808        | 16 A, 1-pole, Hy-Mag | HeT              | 6                        |                                                |                    | Top Feed             |
| EN1809        | 16 A, 1-pole, Hy-Mag | HeT              | 6                        |                                                |                    | Top Feed             |
| EN1812        | 16 A, 1-pole, Hy-Mag | HeT              | 6                        |                                                |                    | Top Feed             |

Table 3/6

| Catalog Number | Input Voltage | Phase    | Max Power Input | Nominal Voltage | On/Off Switch Included | Output Voltage |
|----------------|---------------|----------|-----------------|-----------------|------------------------|----------------|
| EN1403         | 380 – 415V    | 3 PH     | 11.0 kVA        | 415V            | HeT                    | 230VAC         |
| EN1450         | 380 – 415V    | 3 PH     | 11.5 / 11.0 kVA | 415V            | HeT                    | 208 – 230VAC   |
| EN1402         | 400V          | 3 PH WYE | 11.0 kVA        |                 |                        | 200 – 240VAC   |
| EN1811         | 380 – 415V    | 3 PH     | 22.0 kVA        | 415V            | HeT                    | 230VAC         |
| EN1850         | 380 – 415V    | 3 PH     | 17.3 / 22.1 kVA | 415V            | HeT                    | 208 – 230VAC   |
| EN1880         | 380 – 415V    | 3 PH     | 17.3 / 22.1 kVA | 415V            | HeT                    | 208 – 230VAC   |
| EN1950         | 380 – 415V    | 3 PH     | 14.4 kVA        | 415V            | HeT                    | 208 – 230VAC   |

| CatalogNumber | Input Voltage | Phase    | Max Power Input | Nominal Voltage | On/Off Switch Included | Output Voltage |
|---------------|---------------|----------|-----------------|-----------------|------------------------|----------------|
| EN1980        | 380 – 415V    | 3 PH     | 14.4 kVA        | 415V            | Нет                    | 208 – 230VAC   |
| EN1808        | 400V          | 3 PH WYE | 22.0 kVA        |                 |                        | 200 – 240VAC   |
| EN1809        | 400V          | 3 PH WYE | 22.0 kVA        |                 |                        | 200 – 240VAC   |
| EN1812        | 400V          | 3 PH WYE | 22.0 kVA        |                 |                        | 200 – 240VAC   |

Table 4/6

| Catalog Number | Amperage (Derated Amperage)                            | Plug Type              | Rack Units | Removable Input Cable | Metering Type | Material |
|----------------|--------------------------------------------------------|------------------------|------------|-----------------------|---------------|----------|
| EN1403         | 16 A                                                   | IEC 60309 516P6 (IP44) | 0U         | Нет                   | Input         | Сталь    |
| EN1450         | 20 A (16 A)<br>North America,<br>16 A<br>International | IEC 60309 520P6/516P6  | 0U         | Нет                   | Input         | Сталь    |
| EN1402         | 16 A                                                   | IEC 60309 516P6 (IP44) | 0U         | Нет                   | Input         |          |
| EN1811         | 32 A                                                   | IEC 60309 532P6 (IP44) | 0U         | Нет                   | Input         | Сталь    |
| EN1850         | 30 A (24 A)<br>North America,<br>32 A<br>International | IEC 60309 530P6/532P6  | 0U         | Нет                   | Input         | Сталь    |
| EN1880         | 30 A (24 A)<br>North America,<br>32 A<br>International | IEC 60309 530P6/532P6  | 0U         | Нет                   | Input         | Сталь    |
| EN1950         | 60 A (48 A)<br>North America,<br>63 A<br>International | IEC 60309 560P6/563P6  | 0U         | Нет                   | Input         | Сталь    |
| EN1980         | 60 A (48 A)<br>North America,<br>63 A<br>International | IEC 60309 560P6/563P6  | 0U         | Нет                   | Input         | Сталь    |
| EN1808         | 32 A                                                   | IEC 60309 532P6 (IP44) | 0U         | Нет                   | Input         |          |

| CatalogNumber | Amperage<br>(Derated<br>Amperage) | Plug Type                 | Rack Units | Removable<br>Input Cable | Metering Type | Material |
|---------------|-----------------------------------|---------------------------|------------|--------------------------|---------------|----------|
| EN1809        | 32 A                              | IEC 60309<br>532P6 (IP44) | 0U         | Нет                      | Input         |          |
| EN1812        | 32 A                              | IEC 60309<br>532P6 (IP44) | 0U         | Нет                      | Input         |          |

| Table 5/6      |               |           |           |            |         |                  |
|----------------|---------------|-----------|-----------|------------|---------|------------------|
| Catalog Number | Finish        | Высота мм | Ширина мм | Глубина мм | Weight  | Package Quantity |
| EN1403         | Powder Coated | 1750mm    | 52mm      | 53mm       | 7.11kg  | 1                |
| EN1450         | Powder Coated | 1490mm    | 56mm      | 55mm       | 8kg     | 1                |
| EN1402         |               |           |           |            |         | 1                |
| EN1811         | Powder Coated | 1750mm    | 55mm      | 53mm       | 10.22kg | 1                |
| EN1850         | Powder Coated | 1780mm    | 56mm      | 55mm       | 10.5kg  | 1                |
| EN1880         | Powder Coated | 1826mm    | 56mm      | 55mm       | 11.02kg | 1                |
| EN1950         | Powder Coated | 1826mm    | 56mm      | 75mm       | 12.5kg  | 1                |
| EN1980         | Powder Coated | 1826mm    | 56mm      | 75mm       |         | 1                |
| EN1808         |               |           |           |            |         | 1                |
| EN1809         |               |           |           |            |         | 1                |
| EN1812         |               |           |           |            |         | 1                |

| Table 6/6      |                  |
|----------------|------------------|
| Catalog Number | Interrupt Rating |
| EN1403         |                  |
| EN1450         |                  |

| Catalog Number | Interrupt Rating |
|----------------|------------------|
| EN1402         | 5kAIC            |
| EN1811         |                  |
| EN1850         |                  |
| EN1880         |                  |
| EN1950         |                  |
| EN1980         |                  |
| EN1808         | 5kAIC            |
| EN1809         | 5kAIC            |
| EN1812         | 5kAIC            |

## ADDITIONAL PRODUCT DETAILS

---

Please order bracket for vertical mounting separately.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**