

# Outdoor Modular VENT Cabinet

## Power Utilities



Telecom and Railway applications require sophisticated electronics in outdoor setups. nVent SCHROFF Outdoor cabinets shield such electronic components from extreme weather and vandalism, ensuring operational continuity. Modular construction allows multiple configurations in size and function along with multiple cooling options.

## CERTIFICATIONS



## FEATURES

Aluminium profile frame with removable, double-walled cladding

IP 55 or NEMA 12~

Double-walled

Extensive range of 19" cabinet accessories

Access to cabinet from all sides

## SPECIFICATIONS

Table 1/2

| Catalog Number | Product Type    | Product Family | Rack Height | Высота мм | Ширина мм | Глубина мм |
|----------------|-----------------|----------------|-------------|-----------|-----------|------------|
| 10149-337      | Outdoor Cabinet | Modular        | 29 U        | 1530 mm   | 1300 mm   | 630 mm     |
| 10149-334      | Outdoor Cabinet | Modular        | 29 U        | 1530 mm   | 700 mm    | 730 mm     |

| CatalogNumber | Product Type    | Product Family | Rack Height | Высота мм | Ширина мм | Глубина мм |
|---------------|-----------------|----------------|-------------|-----------|-----------|------------|
| 10149-336     | Outdoor Cabinet | Modular        | 29 U        | 1530 mm   | 1300 mm   | 630 mm     |

Table 2/2

| Catalog Number | Wall Type     | Door Type   | Access             | Cooling         | EMC Shielding      | Complies With                                                                                                                           |
|----------------|---------------|-------------|--------------------|-----------------|--------------------|-----------------------------------------------------------------------------------------------------------------------------------------|
| 10149-337      | Double Walled | Double Door | С передней стороны | Fan Ventilation | No (Retrofittable) | IEC 61969-1, IEC 61969-2, IEC 61969-3, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160, ETSI EN 300019-1-4      |
| 10149-334      | Double Walled | Single Door | С передней стороны | Fan Ventilation | No (Retrofittable) | IEC 61969-1, IEC 61969-2, IEC 61969-3, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160, ETSI EN 300019-1-4      |
| 10149-336      | Double Walled | Double Door | С передней стороны | Fan Ventilation | No (Retrofittable) | IEC 61969-1, IEC 61969-2, IEC 61969-3, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160, ETSI EN 300019-1-4, RC2 |

## ADDITIONAL PRODUCT DETAILS

Height dimensions are without base/plinth.

qW = specific heat dissipation capacity according to ETSI EN 300 019-1-4.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**