











CISPEC-2306-0034	E2	UPDATE MOUNTING BUTTON POSITION	2023/07/03	Leo Liu
	E1	INITIAL DRAFT REVIEW	2023/04/13	Leo Liu
ECN/ECO	REV.	DESCRIPTION	DATE	APPROVED

- NOTES :
- INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE AND LOCAL CODES.
 - SEE PRODUCT DOCUMENTATION FOR FURTHER INFORMATION

enLOGIC by nvent

THIS DRAWING AND SPECIFICATIONS HEREIN ARE THE PROPERTY OF CIS GLOBAL AND SHALL NOT BE COPIED, REPRODUCED OR USED IN WHOLE OR IN PART, AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION FROM CIS GLOBAL. THIS DRAWING IS BASED UPON LATEST AVAILABLE INFORMATION AND IS SUBJECT TO CHANGE WITHOUT NOTICE

TITLE : Advantage Series Metered		UNLESS NOTED, DIMENSIONS ARE IN MILLIMETERS & TOLERANCES ARE: X ±1 MM X" ±1" X.X ±0.5 MM X.X" ±0.5" X ±0.20 MM Ø X.X ±0.3 MM Ø X.XX ±0.10 MM		PART NO: EN6881-WXYZ_DA	REV. E2
PROJECT : enLOGIC		BRACKETED DIMENSIONS ARE IN INCHES FOR REFERENCE ONLY THIRD ANGLE PROJECTION INTERPRET PER ASME Y14.5M-1994		DRAWN BY: Leo Liu	2023/04/13
				ENGINEER: Luo Jingbo	2023/07/03
				APPROVED BY: Hanson	2023/07/03
				SCALE : N/A	SHEET 2 OF 3
					SIZE: A3

enLOGIC

RACK Power Distribution Unit

Metered

SKU #: EN1880-WXYZ

Model #: EP112024-0071-L(NA)/EP112032-0071-L(EU)

INPUT: 200-240/346-415VAC, WYE, 3PHASE, 50/60Hz, 24A(NA), OR 200-240/346-415VAC, WYE, 3PHASE, 50/60Hz, 32A(EU)

OUTPUT: C13/C15 LOCKING; 200-240VAC, 10A per outlet

C13/C15/C19 LOCKING; 200-240VAC, 16A max per outlet

24A Total(NA) OR 32A Total(EU)

MAC0 Address:XX-XX-XX-XX-XX-XX

MAC1 Address:XX-XX-XX-XX-XX-XX

Compliance Logos

FC, CE, UKCA, etc.

FCC Rules

EN1880-WXYZ

Serial Number

Notes

1) THIS DEVICE MAY NOT CAUSE HARMFUL INTERFERENCE, AND (2) THIS DEVICE MUST ACCEPT ANY INTERFERENCE RECEIVED, INCLUDING INTERFERENCE THAT MAY CAUSE UNDESIRABLE OPERATION. CAN ICES-3(A)/NMB-3(A)

COMPLIANCE LABEL

NOTES:

1. INTERNAL WIRING

WIRE TYPE: UL AWM 1015, 10&12 & 18 AWG

LINE 1/R/X COLOR: Brown

LINE 2/S/Y COLOR: Black

LINE 3/T/Z COLOR: White

NEUTRAL COLOR: Blue

EARTH GROUND COLOR: Green/Yellow

2. FOR FINISHED GOOD PART NUMBER SEE IDENTIFICATION

INTERNAL WIRING SCHEMATIC DIAGRAM

NOTES:

1. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE AND LOCAL CODES.

2. SEE PRODUCT DOCUMENTATION FOR FURTHER INFORMATION.

3. THIS DRAWING DEPICTS THE POWER SYSTEM CONNECTIONS AND IS NOT REPRESENTATIVE OF THE PHYSICAL LAYOUT. PLEASE REFER TO MECHANICAL DRAWINGS FOR PHYSICAL LAYOUT.

enLOGIC

by nvent

THIS DRAWING AND SPECIFICATIONS HEREIN ARE THE PROPERTY OF CIS GLOBAL AND SHALL NOT BE COPIED, REPRODUCED OR USED IN WHOLE OR IN PART, AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION FROM CIS GLOBAL. THIS DRAWING IS BASED UPON LATEST AVAILABLE INFORMATION AND IS SUBJECT TO CHANGE WITHOUT NOTICE

CISPEC-2306-0034	E2	UPDATE MOUNTING BUTTON POSITION	2023/07/03	Leo Liu
	E1	INITIAL DRAFT REVIEW	2023/04/13	Leo Liu
ECN/ECO	REV.	DESCRIPTION	DATE	APPROVED
REVISIONS				
TITLE :		UNLESS NOTED, DIMENSIONS ARE IN MILLIMETERS & TOLERANCES ARE:		PART NO: EN6881-WXYZ_DA
Advantage Series		X ±1 MM X" ±1"		REV. E2
Metered		X.X ±0.5 MM X.X" ±0.5"		DRAWN BY: Leo Liu
		X ±0.20 MM		2023/04/13
		Ø X.X ±0.3 MM		ENGINEER: Luo Jingbo
		Ø X.XX ±0.10 MM		2023/07/03
		BRACKETED DIMENSIONS ARE IN INCHES FOR REFERENCE ONLY		APPROVED BY: Hanson
		THIRD ANGLE PROJECTION		2023/07/03
PROJECT :		enLOGIC		SCALE : N/A
		INTERPRET PER ASME Y14.5M-1994		SHEET 3 OF 3
				SIZE: A3