



1. MAKE SURE ALL COUPLERS ARE SCREWED COMPLETELY ON THE STRAIGHT-THREADED MALE
2. WITH THE CAGE BOTTOMED OUT, VERIFY THAT ALL TAPERED MALE ENDS ARE FLUSH WITH THE COUPLER MOUTH OR INSIDE THE COUPLER



This document and the contents thereof is the property of nVent and is furnished to you for information only. All dimensions and tolerances are in inches [mm], unless otherwise specified. Revisions are to be computer processed. No manual changes permitted. This document is not to be used as an instruction sheet.

**WARNING:**

1. nVent products shall be installed and used only as indicated in nVent product instruction sheets and training materials. Instruction sheets are available at [www.nVent.com](http://www.nVent.com) and from your nVent customer service representative.
2. nVent products must never be used for a purpose other than the purpose for which they were designed or in a manner that exceeds specified load ratings.
3. All instructions must be completely followed to ensure proper and safe installation and performance.
4. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and/or death, and void your warranty.

The customer is responsible for:



- a. Conformance to all governing codes.
- b. The integrity of structures to which the products are attached, including their capability of safely accepting the loads imposed, as evaluated by a qualified engineer.
- c. Using appropriate industry standard hardware as noted above.

**SAFETY INSTRUCTIONS:**

All governing codes and regulations and those required by the job site must be observed. Always use appropriate safety equipment such as eye protection, hard hat, and gloves as appropriate to the application.

nVent, CADDY, ERICO CADWELD, ERICO CRITEC, ERICO, ERIFLEX, and LENTON are owned by nVent or its global affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without prior notice.

Bar Size		Max Bar End Gap	Part Numbers		
US	Metric	in [mm]	Male-Taper	Male-Parallel	Coupler
#4	12	0.8 [21]	LU12MT12(D)	LU12MS15(D)	LU12PT15(D)
#5	16	1.1 [27]	LU16MT12(D)	LU16MS15(D)	LU16PT15(D)
#6	20	1.5 [39]	LU20MT12(D)	LU20MS15(D)	LU20PT15(D)
#7	22	1.6 [41]	LU22MT12(D)	LU22MS15(D)	LU22PT15(D)
#8	25	1.7 [44]	LU25MT12(D)	LU25MS15(D)	LU25PT15(D)
#9	28	1.8 [46]	LU28MT12(D)	LU28MS15(D)	LU28PT15(D)
#10	32	2.0 [50]	LU32MT12(D)	LU32MS15(D)	LU32PT15(D)
#11	36	2.2 [56]	LU36MT12(D)	LU36MS15(D)	LU36PT15(D)
#14	43	2.9 [74]	LU43TMT12(D)	LU43TMS15(D)	LU43TPT15(D)
#18	57	3.6 [91]	LU57TMT12(D)	LU57TMS15(D)	LU57TPT15(D)

Tolerance (Inch) Unless Noted				Third Angle Projection 	
Angular Tolerance: ±1°		Title: REFERENCE SHEET LENTON ULTIMATE PT15 POSITIONAL COUPLER			
Fractional Tolerance: ±1/32					
Two Place Decimal: ±0.01					
Three Place Decimal: ±0.005					
Tolerance [mm] Unless Noted		Scale: DWG None  CRSLUP REV A			
Angular Tolerance: ±1°					
One Place Decimal: ±0.3					
Two Place Decimal: ±0.13					
B Size	SHT 1 Of 1				