






NOTES:
1. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE AND LOCAL CODES.
2. PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSIONS ARE IN [INCHES]
3. UNIVERSAL MOUNTING BRACKET IS AN ALTERNATIVE MOUNTING METHOD TO THE TOOLLESS MOUNT FOR 3RD PARTY ENCLOSURES. BRACKET IS PROVIDED WITH THE UNIT.
4. DETAILED INSTALLATION INSTRUCTIONS CAN BE FOUND IN THE QUICK START GUIDE
5. CONNECT EXTERNAL EARTH GROUND TOTHE 10-32 SIZE THREADED NUT
6. SEE PRODUCT DOCUMENTATION FOR FURTHER INFORMATION
7. INPUT PLUG CONFIGURATION (SEE IDENTIFICATION TABLE) FOR DUAL-RATED UNITS, NEMA PLUGS ARE NAM RATED ONLY AND CAPTIVE AUS/NZ PLUGS ARE EMEA RATED ONLY




TECHNICAL SPECIFICATIONS	
UNIT TYPE:	INPUT METERED
ORIENTATION:	HORIZONTAL, 2U
OUTLET QTY & TYPE:	(18)C13/C15/C19
INPUT VOLTAGE:	200-240VAC
INPUT CURRENT:	100A(80A DERATED)
BREAKER QTY & TYPE:	(9) 20AMP, DOUBLE-POLE, 10KAIC
INPUT PHASE:	THREE-PHASE, DELTA
RATED POWER:	28.8kVA
INPUT PLUG:	SEE IDENTIFICATION TABLE
INPUT POWER CORD:	SEE IDENTIFICATION TABLE


FEATURES	
METERING ATTRIBUTES	VOLTAGE(V), CURRENT(A), APPARENT POWER(kVA), REAL POWER(kW), POWER FACTOR, ENERGY(kWh)
METERED COMPONENTS	INPUT (PHASE)
REMOTE OUTLET SWITCHING	NO
ENVIRONMENTAL CONDITIONS	
OPERATING TEMPERATURE	-5 TO 60 C (23 TO 140 F)
STORAGE TEMPERATURE	-20 TO 60 C (-4 TO 140 F)
HUMIDITY (OPERATING/STORAGE)	5-90% RH / 5-95% RH; NON-CONDENSING
MAX OPERATING ELEVATION, ABOVE MSL	3000M (9840 FT)
COMPLIANCE	
SAFETY & ENVIRONMENTAL	IEC 62368-1 LISTED, FCC, CSA, RoHS COMPLIANT

IDENTIFICATION TABLE	EN1964 - * * * *			
MODEL IS SHOWN IN DEFAULT CONFIGURATION. FOR OPTIONAL CONFIGURATIONS, USE ITEM IDENTIFIER CODE IN PLACE OF EACH ASTERISK. ORDERABLE BASED ON FORMAT: SKU NUMBER - * * * *	INPUT PLUG	CHASSIS COLOR	CORD OPTION	ORIENTATION
	(DEFAULT) 4100P9W(IP67) = 0	(DEFAULT) BLACK = 0	(DEFAULT) 1.8m [6'] = 0 1m [3.2'] = 1 2m [6.6'] = 2 3m [10'] = 3	(DEFAULT) FRONT FACING BRKT, REAR INPUT = 0
OPTIONS LISTED ON THIS ROW ARE NON STANDARD, CONTACT SALES FOR ADDITIONAL INFORMATION		BLUE = B RED = R WHITE = W GREEN = G YELLOW = Y ORANGE = A	0.5m [1.6'] = A 4.5m [14.7'] = E 1.5m [4.9'] = B 1.2m [4'] = G 2.5m [8.2'] = C 3.65m [12'] = H 3.5m [11.5'] = D	




THIS DRAWING AND SPECIFICATIONS HEREIN ARE THE PROPERTY OF NVENT AND SHALL NOT BE COPIED, REPRODUCED OR USED IN WHOLE OR IN PART, AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION FROM NVENT. THIS DRAWING IS BASED UPON LATEST AVAILABLE INFORMATION AND IS SUBJECT TO CHANGE WITHOUT NOTICE

	E1	INITIAL DRAFT REVIEW				2024-12-03	Leo
ECN/ECO	REV.	DESCRIPTION				DATE	DRAWING BY
REVISIONS							
TITLE: ADVANTAGE SERIES MONITORED INPUT		UNLESS NOTED, DIMENSIONS ARE IN MILLIMETERS & TOLERANCES ARE: X. ±1 MM X° ±1° X.X ±0.5 MM X.X° ±0.5° X.XX ±0.20 MM Ø X.X ±0.3 MM Ø X.XX ±0.10 MM BRACKETED DIMENSIONS ARE IN INCHES FOR REFERENCE ONLY ⊕  THRID ANGLE PROJECTION INTERPRET PER ASME Y14.5M-1994		PART NO: EN1964-WXYZ_DA		REV. E1	
				DRAWN BY: Leo Liu		2024-12-03	
				ENGINEER: FYZ		2024-12-03	
				APPROVED BY: LJB		2024-12-03	
				SCALE:1:5 (DO NOT SCALE DRAWING)		SHEET 1 OF 3	
PROJECT: ENLOGIC							




NMC PANEL


FRONT VIEW



REAR VIEW



NOTES:
1. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE AND LOCAL CODES.
2. SEE PRODUCT DOCUMENTATION FOR FURTHER INFORMATION



THIS DRAWING AND SPECIFICATIONS HEREIN ARE THE PROPERTY OF NVENT AND SHALL NOT BE COPIED, REPRODUCED OR USED IN WHOLE OR IN PART, AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION FROM NVENT. THIS DRAWING IS BASED UPON LATEST AVAILABLE INFORMATION AND IS SUBJECT TO CHANGE WITHOUT NOTICE

TITLE:
ADVANTAGE SERIES
MONITORED INPUT

PROJECT:
ENLOGIC

UNLESS NOTED, DIMENSIONS ARE IN MILLIMETERS & TOLERANCES ARE:
X. ±1 MM X° ±1°
X.X ±0.5 MM X.X° ±0.5°
X.XX ±0.20 MM
ØX.X ±0.3 MM
ØX.XX ±0.10 MM
BRACKETED DIMENSIONS ARE IN INCHES FOR REFERENCE ONLY
⊕ THRID ANGLE PROJECTION
INTERPRET PER ASME Y14.5M-1994

PART NO: EN1964-WXYZ_DA		REV. E1	
DRAWN BY: Leo Liu		2024-12-03	
ENGINEER: FYZ		2024-12-03	
APPROVED BY: LJB		2024-12-03	
SCALE:2:1 (DO NOT SCALE DRAWING)		SHEET 2 OF 3	SIZE: A1

ENLOGIC

RACK Power Distribution Unit
Metered


Made In XXXXX

SKU #: EN1964-WXYZ
Model #: EP114280-0100-C
INPUT: 200-240VAC, DELTA, 3-PHASE, 50/60Hz, 80A
OUTPUT: C13/C15/C19 COMBO; 200-240VAC, 16A max per outlet



SKU#:

EN1964-WXYZ



Serial Number

XXXXXXXX XX X X

THIS DEVICE COMPLIES WITH PART 15 OF THE FCC RULES.
OPERATION IS SUBJECT TO THE FOLLOWING TWO CONDITIONS:
(1) THIS DEVICE MAY NOT CAUSE HARMFUL INTERFERENCE,
AND (2) THIS DEVICE MUST ACCEPT ANY INTERFERENCE RECEIVED,
INCLUDING INTERFERENCE THAT MAY CAUSE UNDESIRED OPERATION.
CAN1CES-003(A)/NMB-003(A)

MAC0 Address:XX-XX-XX-XX-XX-XX
MAC1 Address:XX-XX-XX-XX-XX-XX

COMPLIANCE LABEL

NOTES :

1.INTERNAL WIRING

WIRE TYPE:

LINE 1/R/X COLOR:

LINE 2/S/Y COLOR:

LINE 3/T/Z COLOR:

EARTH GROUND COLOR:

DESIGN^(PDU)
ENGINEERING

UL AWM 1015,10 & 12 & 18 AWG


Black

Orange

Red

Green/Yellow


2.FOR FINISHED GOOD PART NUMBER SEE IDENTIFICATION



INTERNAL WIRING SCHEMATIC

NOTES:

1. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE AND LOCAL CODES.
2. SEE PRODUCT DOCUMENTATION FOR FURTHER INFORMATION
3. THIS DRAWING DEPICTS THE POWER SYSTEM CONNECTIONS AND IS NOT REPRESENTATIVE OF THE PHYSICAL LAYOUT. PLEASE REFER TO MECHANICAL DRAWINGS FOR PHYSICAL LAYOUT



THIS DRAWING AND SPECIFICATIONS
HEREIN ARE THE PROPERTY OF NVENT
AND SHALL NOT BE COPIED,
REPRODUCED OR USED IN
WHOLE OR IN PART, AS THE BASIS FOR THE
MANUFACTURE OR SALE OF ITEMS
WITHOUT WRITTEN PERMISSION FROM
NVENT. THIS DRAWING IS BASED UPON
LATEST AVAILABLE INFORMATION AND IS
SUBJECT TO CHANGE WITHOUT NOTICE

TITLE:

ADVANTAGE SERIES
MONITORED INPUT

PROJECT:

ENLOGIC

UNLESS NOTED, DIMENSIONS ARE IN
MILLIMETERS & TOLERANCES ARE:

X. ±1 MM X° ±1°
X.X ±0.5 MM X.X° ±0.5°
X.XX ±0.20 MM
ØX.X ±0.3 MM
ØX.XX ±0.10 MM

BRACKETED DIMENSIONS ARE IN
INCHES FOR REFERENCE ONLY

⊕ THRID ANGLE PROJECTION
INTERPRET PER ASME Y14.5M-1994

PART NO:

EN1964-WXYZ_DA

DRAWN BY: Leo Liu

ENGINEER: FYZ

APPROVED BY: LJB

SCALE:1:1

(DO NOT SCALE DRAWING)

REV.

E1

2024-12-03

2024-12-03

2024-12-03

SHEET

3 OF 3

SIZE:

A1