



Opis: Busbar support up to 1600A to be mounted horizontally or vertically. Mounts directly to the enclosure frame or with help of CLPF profiles. Available in single and double bar per phase for bar thickness 5 mm and only single bar per phase for bar thickness 10 mm, and width from 25 to 80 mm.

Temperatura robocza: -40°C up to 130°C.

Material: Reinforced polyamide and steel. Halogen free.

Dostawa: Busbar support with mounting material.

Nr pozycji
ECBS205TN
ECBS110TN