




NOTES:


1. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE AND LOCAL CODES.
2. PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSIONS ARE IN [INCHES]
3. UNIVERSAL MOUNTING BRACKET IS AN ALTERNATIVE MOUNTING METHOD TO THE TOOLLESS MOUNT FOR 3RD PARTY ENCLOSURES. BRACKET IS PROVIDED WITH THE UNIT.
4. DETAILED INSTALLATION INSTRUCTIONS CAN BE FOUND IN THE QUICK START GUIDE
5. CONNECT EXTERNAL EARTH GROUND TO THE 10-32 SIZE THREADED NUT
6. SEE PRODUCT DOCUMENTATION FOR FURTHER INFORMATION
7. INPUT PLUG CONFIGURATION (SEE IDENTIFICATION TABLE) FOR DUAL-RATED UNITS, NEMA PLUGS ARE NAM RATED ONLY AND CAPTIVE AUS/NZ PLUGS ARE EMEA RATED ONLY




REAR VIEW



TOP VIEW



FRONT VIEW




SIDE VIEW

TECHNICAL SPECIFICATIONS	
UNIT TYPE:	METERED & SWITCHED PER OUTLET
ORIENTATION:	HORIZONTAL, 2U
OUTLET QTY & TYPE:	(6)C13/C15 COMBO, (6)C13/C15/C19 COMBO
INPUT VOLTAGE:	200-240VAC
INPUT CURRENT:	60A(48A DERATED)(NAM)/63A(EU)
BREAKER QTY & TYPE:	(4) 20AMP, SINGLE-POLE,5KAIC
INPUT PHASE:	SINGLE-PHASE
RATED POWER:	DUAL-RATED 11.5kVA(NAM)/14.5kVA(EU)
INPUT PLUG:	SEE IDENTIFICATION TABLE
INPUT POWER CORD:	SEE IDENTIFICATION TABLE
FEATURES	
METERING ATTRIBUTES	VOLTAGE(V), CURRENT(A), APPARENT POWER(kVA), REAL POWER(kW), POWER FACTOR, ENERGY(kWh)
METERED COMPONENTS	INPUT (PHASE), BREAKERS , OUTLETS
REMOTE OUTLET SWITCHING	YES
ENVIRONMENTAL CONDITIONS	
OPERATING TEMPERATURE	-5 TO 60 C (23 TO 140 F)
STORAGE TEMPERATURE	-20 TO 60 C (-4 TO 140 F)
HUMIDITY (OPERATING/STORAGE)	5-90% RH / 5-95% RH; NON-CONDENSING
MAX OPERATING ELEVATION, ABOVE MSL	3000M (9840 FT)
COMPLIANCE	
SAFETY & ENVIRONMENTAL	IEC 62368-1 LISTED, CE,UKCA, CSA,FCC,RoHS COMPLIANT

IDENTIFICATION TABLE		* INPUT PLUG		* CHASSIS COLOR		* CORD OPTION		* ORIENTATION	
MODEL IS SHOWN IN DEFAULT CONFIGURATION. FOR OPTIONAL CONFIGURATIONS, USE ITEM IDENTIFIER CODE IN PLACE OF EACH ASTERISK. ORDERABLE BASED ON FORMAT: SKU NUMBER - ****		(DEFAULT)360P6/363P6(IP44)=0 (OPTIONAL)363P6W(IP67) = M		(DEFAULT) BLACK = 0		(DEFAULT) 3m [10"] = 0 1m [3.2"] = 1 2m [6.6"] = 2		(DEFAULT)FRONT FACING BRKT,REAR INPUT=0	
OPTIONS LISTED ON THIS ROW ARE NON STANDARD, CONTACT SALES FOR ADDITIONAL INFORMATION				BLUE = B RED = R WHITE = W GREEN = G YELLOW = Y ORANGE = A		0.5m [1.6"] = A 4.5m [14.7"] = E 1.5m [4.9"] = B 1.2m [4"] = G 2.5m [8.2"] = C 3.65m [12"] = H 3.5m [11.5"] = D 1.8m [6"] = F			

		E1	INITIAL DRAFT REVIEW					2024/10/09		CCQ	
ECN/ECO		REV.	DESCRIPTION					DATE		DRAWING BY	
REVISIONS											
TITLE:			UNLESS NOTED, DIMENSIONS ARE IN MILLIMETERS & TOLERANCES ARE: <div><div>X. ±1 MM</div><div>X.X ±0.5 MM</div><div>X.XX ±0.20 MM</div><div>Ø X.X ±0.3 MM</div><div>Ø X.XX ±0.10 MM</div></div> BRACKETED DIMENSIONS ARE IN INCHES FOR REFERENCE ONLY ⊕ ≡ THRD ANGLE PROJECTION INTERPRET PER ASME Y14.5M-1994				PART NO: EN6354-WXYZ			REV. E1	
ADVANTAGE SERIES METERED&SWITCHED PER OUTLET							DRAWN BY: CCQ			2024/10/09	
							ENGINEER: Yuzhou Feng			2024/10/09	
							APPROVED BY: LJB			2024/10/09	
PROJECT:							SCALE:1:5 (DO NOT SCALE DRAWING)			SHEET 1 OF 3	SIZE: A1
ENLOGIC											



THIS DRAWING AND SPECIFICATIONS
HEREIN ARE THE PROPERTY OF NVENT
AND SHALL NOT BE COPIED,
REPRODUCED OR USED IN
WHOLE OR IN PART, AS THE BASIS FOR THE
MANUFACTURE OR SALE OF ITEMS
WITHOUT WRITTEN PERMISSION FROM
NVENT. THIS DRAWING IS BASED UPON
LATEST AVAILABLE INFORMATION AND IS
SUBJECT TO CHANGE WITHOUT NOTICE

TITLE:


ADVANTAGE SERIES
METERED&SWITCHED
PER OUTLET

PROJECT: **ENLOGIC**

UNLESS NOTED, DIMENSIONS ARE IN MILLIMETERS & TOLERANCES ARE:

X.	± 1	MM	X°	$\pm 1^\circ$
X.X	± 0.5	MM	X.X°	$\pm 0.5^\circ$
X.XX	± 0.20	MM		
Ø X.X	± 0.3	MM		
Ø X.XX	± 0.10	MM		

BRACKETED DIMENSIONS ARE IN INCHES FOR REFERENCE ONLY

 THIRD ANGLE PROJECTION

INTERPRET PER ASME Y14.5M-1994

PART NO:
EN6354-WXYZ


DRAWN BY: CCQ

ENGINEER: Yuzhou Feng


APPROVED BY: LJB

SCALE:1:5
(DO NOT SCALE DRAWING)

REV.		E1
2024/10/09		
2024/10/09		
2024/10/09		
SHEET 1 OF 3	SIZE: A1	





FRONT VIEW



REAR VIEW

STANDARD RECEPTACLES

RECEPTACLE




COMBO C13/C15
10A, 250V, MAX
RATED OUTPUT

COMBO C13/C15/C19
16A, 250V, MAX
RATED OUTPUT


INPUT PLUG

(DEFAULT)




IEC 60309,2P 3W 6H
IP44(SPLASHPROOF)
250V MAX RATED INPUT
60A(48A DERATED)/63A

OPTIONAL



IEC 60309,2P 3W 6H
IP67(WATERTIGHT)
250V MAX RATED INPUT
60A(48A DERATED)/63A

- NOTES:
- 1. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE AND LOCAL CODES.
 - 2. SEE PRODUCT DOCUMENTATION FOR FURTHER INFORMATION



THIS DRAWING AND SPECIFICATIONS HEREIN ARE THE PROPERTY OF NVENT AND SHALL NOT BE COPIED, REPRODUCED OR USED IN WHOLE OR IN PART, AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION FROM NVENT. THIS DRAWING IS BASED UPON LATEST AVAILABLE INFORMATION AND IS SUBJECT TO CHANGE WITHOUT NOTICE

TITLE:

ADVANTAGE SERIES
METERED&SWITCHED
PER OUTLET

PROJECT:

ENLOGIC

UNLESS NOTED, DIMENSIONS ARE IN MILLIMETERS & TOLERANCES ARE:
X. ±1 MM X° ±1°
X.X ±0.5 MM X.X° ±0.5°
X.XX ±0.20 MM
ØX.X ±0.3 MM
ØX.XX ±0.10 MM
BRACKETED DIMENSIONS ARE IN INCHES FOR REFERENCE ONLY
⊕ THRID ANGLE PROJECTION
INTERPRET PER ASME Y14.5M-1994

PART NO: EN6354-WXYZ	REV. E1
DRAWN BY: CCQ	2024/10/09
ENGINEER: Yuzhou Feng	2024/10/09
APPROVED BY: LJB	2024/10/09
SCALE:2:1 (DO NOT SCALE DRAWING)	SHEET 2 OF 3 SIZE: A1

ENLOGIC

RACK Power Distribution Unit

Metered&Switched per outlet

SKU #: EN6354-WXYZ
Model #: EP161248-0068-C(NA)/EP161263-0068-C(EU)
INPUT: 200-240VAC,1-PHASE,50/60Hz, 48A(NA),OR
200-240VAC,1-PHASE,50/60Hz, 63A(EU)
OUTPUT: C13/C15 COMBO; 200-240VAC, 10A per outlet
C13/C15/C19 COMBO; 200-240VAC, 16A max per outlet
48A Total(NA) OR 63A Total(EU)

MAC0 Address:XX-XX-XX-XX-XX-XX
MAC1 Address:XX-XX-XX-XX-XX-XX

Made In XXXXX

50

UK

CA

FC

C

300805

US

CE

nVent
8th Floor The Mills 1000
Great West Road
BRENTFORD,
TW9 9DW United Kingdom

SCHROFF GmbH
Langenalberr Str. 96-100
75354 Straubenhardt
Germany

SKU#:
E N 6 3 5 4 -W X Y Z

Serial Number
XXXXXXXXXX

THIS DEVICE COMPLIES WITH PART 15 OF THE FCC RULES.
OPERATION IS SUBJECT TO THE FOLLOWING TWO CONDITIONS:
(1) THIS DEVICE MAY NOT CAUSE HARMFUL INTERFERENCE,
AND (2) THIS DEVICE MUST ACCEPT ANY INTERFERENCE RECEIVED,
INCLUDING INTERFERENCE THAT MAY CAUSE UNDESIRED OPERATION.
CAN ICES-003(A)/NMB-003(A)

NOTES:
1.INTERNAL WIRING
WIRE TYPE: UL AWM 1015,10 & 12 & 18 AWG
LINE 1/R/X COLOR: BROWN
NEUTRAL COLOR: BLUE
EARTH GROUND COLOR: GREEN/YELLOW
2.FOR FINISHED GOOD PART NUMBER-SEE IDENTIFICATION

COMPLIANCE LABEL

INTERNAL WIRING SCHEMATIC

NOTES:

- 1. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE AND LOCAL CODES.
- 2. SEE PRODUCT DOCUMENTATION FOR FURTHER INFORMATION
- 3. THIS DRAWING DEPICTS THE POWER SYSTEM CONNECTIONS AND IS NOT REPRESENTATIVE OF THE PHYSICAL LAYOUT. PLEASE REFER TO MECHANICAL DRAWINGS FOR PHYSICAL LAYOUT

THIS DRAWING AND SPECIFICATIONS HEREIN ARE THE PROPERTY OF NVENT AND SHALL NOT BE COPIED, REPRODUCED OR USED IN WHOLE OR IN PART, AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION FROM NVENT. THIS DRAWING IS BASED UPON LATEST AVAILABLE INFORMATION AND IS SUBJECT TO CHANGE WITHOUT NOTICE

TITLE:

ADVANTAGE SERIES
METERED&SWITCHED
PER OUTLET

PROJECT:

ENLOGIC

UNLESS NOTED, DIMENSIONS ARE IN MILLIMETERS & TOLERANCES ARE:
X. ±1 MM X° ±1°
X.X ±0.5 MM X.X° ±0.5°
X.XX ±0.20 MM
Ø X.X ±0.3 MM
Ø X.XX ±0.10 MM
BRACKETED DIMENSIONS ARE IN INCHES FOR REFERENCE ONLY
⊕ THRID ANGLE PROJECTION
INTERPRET PER ASME Y14.5M-1994

PART NO: EN6354-WXYZ	REV. E1
DRAWN BY: CCQ	2024/10/09
ENGINEER: Yuzhou Feng	2024/10/09
APPROVED BY: LJB	2024/10/09
SCALE:1:1 (DO NOT SCALE DRAWING)	SHEET 3 OF 3 SIZE: A1