




TECHNICAL SPECIFICATIONS	
UNIT TYPE:	MONITORED INPUT
ORIENTATION:	VERTICAL, MID
OUTLET QTY & TYPE:	(20)C13/C15,(20)C13/C15/C19
INPUT VOLTAGE:	200-240VAC
INPUT CURRENT:	32A
BREAKER QTY & TYPE:	(2)20AMP, SINGLE-POLE
INPUT PHASE:	SINGLE-PHASE
RATED POWER:	7.4 KVA
INPUT PLUG:	SEE NOTE 7
INPUT POWER CORD:	SEE IDENTIFICATION TABLE
FEATURES	
METERING ACCURACY	+/-1% TO ISO/ IEC 62052-21
METERING ATTRIBUTES	VOLTAGE(V), CURRENT(A), APPARENT POWER(kVA), REAL POWER(kW), POWER FACTOR, ENERGY(kWh)
METERED COMPONENTS	INPUT(PHASE), CIRCUIT BREAKERS
REMOTE OUTLET SWITCHING	N/A
ENVIRONMENTAL CONDITIONS	
OPERATING TEMPERATURE	-5 TO 60 C (23 TO 140 F)
STORAGE TEMPERATURE	-20 TO 60 C (-4 TO 140 F)
HUMIDITY (OPERATING/STORAGE)	5-90% RH / 5-95% RH; NON-CONDENSING
MAX OPERATING ELEVATION, ABOVE MSL	3000M(9840FT)
COMPLIANCE	
SAFETY&ENVIRONMENTAL	RoHS COMPLIANT

IDENTIFICATION TABLE	EN1350-	*	*	*	*
MODEL IS SHOWN IN DEFAULT CONFIGURATION. FOR OPTIONAL CONFIGURATIONS, USE ITEM IDENTIFIER CODE IN PLACE OF EACH ASTERISK. ORDERABLE BASED ON FORMAT: EN1350-****	INPUT PLUG (DEFAULT)332P6(IP44)=0	CHASSIS COLOR (DEFAULT) BLACK = 0 BLUE = B RED = R WHITE = W GREEN = G YELLOW = Y	CORD OPTION (DEFAULT) 3m [10'] = 0 1m [3.2'] = 1 2m [6.6'] = 2 3m [10'] = 3	ORIENTATION (DEFAULT) TOP FEED = 0 BOTTOM FEED = 2	
OPTIONS LISTED ON THIS ROW ARE NON STANDARD, CONTACT SALES FOR ADDITIONAL INFORMATION	(OPTIONAL)332P6W(IP67)=J	ORANGE = A	0.5m [1.6'] = A 1.2m [4'] = G 1.5m [4.9'] = B 1.8m [6'] = F 2.5m [8.2'] = C		


- NOTES :
1. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE AND LOCAL CODES.
 2. PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSIONS ARE IN [INCHES]
 3. UNIVERSAL MOUNTING BRACKET IS AN ALTERNATIVE MOUNTING METHOD TO THE TOOLLESS MOUNT FOR 3RD PARTY ENCLOSURES. BRACKET IS PROVIDED WITH THE UNIT.
 4. DETAILED INSTALLATION INSTRUCTIONS CAN BE FOUND IN THE QUICK START GUIDE
 5. CONNECT EXTERNAL EARTH GROUND TO THE 10-32 SIZE THREADED NUT
 6. SEE PRODUCT DOCUMENTATION FOR FURTHER INFORMATION
 7. INPUT PLUG CONFIGURATION (SEE IDENTIFICATION TABLE) FOR DUAL-RATED UNITS, NEMA PLUGS ARE NAM RATED ONLY AND CAPTIVE AUS/NZ PLUGS ARE EMEA RATED ONLY




THIS DRAWING AND SPECIFICATIONS HEREIN ARE THE PROPERTY OF CIS GLOBAL AND SHALL NOT BE COPIED, REPRODUCED OR USED IN WHOLE OR IN PART, AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION FROM CIS GLOBAL. THIS DRAWING IS BASED UPON LATEST AVAILABLE INFORMATION AND IS SUBJECT TO CHANGE WITHOUT NOTICE

	E1	INITIAL DRAFT REVIEW		2023/03/29	LRF	
ECN/ECO	REV.	DESCRIPTION		DATE	APPROVED	
REVISIONS						
TITLE : Advantage Series Metered		UNLESS NOTED, DIMENSIONS ARE IN MILLIMETERS & TOLERANCES ARE: X ±1 MM X" ±1" X.X ±0.5 MM X.X" ±0.5" X ±0.20 MM Ø X.X ±0.3 MM Ø X.XX ±0.10 MM BRACKETED DIMENSIONS ARE IN INCHES FOR REFERENCE ONLY ④  THIRD ANGLE PROJECTION INTERPRET PER ASME Y14.5M-1994		PART NO: EN1350-WXYZ_DA		REV. E1
				DRAWN BY: LRF		2023/03/29
				ENGINEER: LJB		2023/03/29
				APPROVED BY: Hanson		2023/03/29
				SCALE : N/A		SHEET 1 OF 3
PROJECT : enLOGIC						

DESIGN (PDU)
ENGINEERING





RECEPTACLE




C13/C15 COMBO
10A, 250V MAX
RATED OUTPUT

C13/C15/C19 COMBO
16A, 250V MAX
RATED OUTPUT



- Critical Alarm Alerts
- PDU Alarm
 - Cascade Error
 - Environmental Alarm
 - Security Alarm
 - Circuit Breaker Alarm
- Source Color Coding (User Selected Option)
- User Interactive Display (for setup and detailed information)
- 10/100 Ethernet Port (for redundancy and Ethernet cascading)
- Digital Sensor Port 2



NOTES:

1. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE AND LOCAL CODES.
2. SEE PRODUCT DOCUMENTATION FOR FURTHER INFORMATION

enLOGIC by nvent

THIS DRAWING AND SPECIFICATIONS HEREIN ARE THE PROPERTY OF CIS GLOBAL AND SHALL NOT BE COPIED, REPRODUCED OR USED IN WHOLE OR IN PART, AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION FROM CIS GLOBAL. THIS DRAWING IS BASED UPON LATEST AVAILABLE INFORMATION AND IS SUBJECT TO CHANGE WITHOUT NOTICE

TITLE:

Advantage Series
Metered

PROJECT:

enLOGIC

UNLESS NOTED, DIMENSIONS ARE IN MILLIMETERS & TOLERANCES ARE:

X	±1 MM	X"	±1"
X.X	±0.5 MM	X.X"	±0.5"
X.XX	±0.20 MM		
Ø X.X	±0.3 MM		
Ø X.XX	±0.10 MM		

BRACKETED DIMENSIONS ARE IN INCHES FOR REFERENCE ONLY

THIRD ANGLE PROJECTION

INTERPRET PER ASME Y14.5M-1994

PART NO:	EN1350-WXYZ_DA	REV.	E1
DRAWN BY:	LRF	2023/03/29	
ENGINEER:	LJB	2023/03/29	
APPROVED BY:	Hanson	2023/03/29	
SCALE:	N/A	SHEET	2 OF 3
		SIZE:	A3

enLOGIC

RACK Power Distribution Unit

Metered

Made in XXXXX

SKU#:

EN1350-WXYZ

Model #:

EP111032-0060-C

INPUT:

200-240VAC, 1PHASE, 50/60Hz, 32A

OUTPUT:

C13/C15 COMBO; 200-240VAC, 10A per outlet

C13/C15/C19 COMBO;

200-240VAC, 16A max per outlet

32A Total

MAC0 Address:

XX-XX-XX-XX-XX

MAC1 Address:

XX-XX-XX-XX-XX

N

CE

UK

CA

CIS Global LLC

1001 W COMMERCE

ST THOSOM, AZ 85746

Serial Number

EN1350-WXYZ

COMPLIANCE LABEL

NOTES:

1. INTERNAL WIRING

WIRE TYPE:

UL AWM 1015,10 & 12 & 18 AWG

LINE 1/R/X COLOR:

BROWN

EARTH GROUND COLOR:

GREEN

NEUTRAL COLOR:

BLUE

2. FOR FINISHED GOOD PART NUMBER SEE IDENTIFICATION

INTERNAL WIRING SCHEMATIC DIAGRAM

NOTES:

1. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE AND LOCAL CODES.

2. SEE PRODUCT DOCUMENTATION FOR FURTHER INFORMATION

3. THIS DRAWING DEPICTS THE POWER SYSTEM CONNECTIONS AND IS NOT REPRESENTATIVE OF THE PHYSICAL LAYOUT. PLEASE REFER TO MECHANICAL DRAWINGS FOR PHYSICAL LAYOUT.

enLOGIC

by nvent

THIS DRAWING AND SPECIFICATIONS HEREIN ARE THE PROPERTY OF CIS GLOBAL AND SHALL NOT BE COPIED, REPRODUCED OR USED IN WHOLE OR IN PART, AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION FROM CIS GLOBAL. THIS DRAWING IS BASED UPON LATEST AVAILABLE INFORMATION AND IS SUBJECT TO CHANGE WITHOUT NOTICE

TITLE:

Advantage Series Metered

PROJECT:

enLOGIC

UNLESS NOTED, DIMENSIONS ARE IN MILLIMETERS & TOLERANCES ARE:

X. ±1 MM

X.X ±0.5 MM

X.XX ±0.20 MM

Ø X.X ±0.3 MM

Ø X.XX ±0.10 MM

X" ±1"

X.X" ±0.5"

BRACKETED DIMENSIONS ARE IN INCHES FOR REFERENCE ONLY

THIRD ANGLE PROJECTION

INTERPRET PER ASME Y14.5M-1994

PART NO:

EN1350-WXYZ_DA

REV:

E1

DRAWN BY:

LRF

2023/03/29

ENGINEER:

LJB

2023/03/29

APPROVED BY:

Hanson

2023/03/29

SCALE:

N/A

SHEET

3 OF 3

SIZE:

A3