


ENEC LICENSE

License No. ENEC-04005-M2

Page 1/3

Date of Issue 2023-10-12

License Holder	PFEIFER UND SEIBEL GMBH MAURERSTRASSE 15 BREIDENBACH, 35236 GERMANY
Production site	PFEIFER UND SEIBEL GMBH MAURERSTRASSE 15 BREIDENBACH, 35236 GERMANY
Certification Mark	See Annex 1
Certified Product	Surface mounted LED luminaire
Model	CEL550M See Page 2
Trademark	
Ratings	5.1 W 24 V - 240 V DC/AC 50/60 Hz Class II IP20 ta=55 °C See Page 2 for additional ratings
Tested acc. to	EN 60598-2-1:1989, EN 60598-1:2015, EN 60598-1:2015/A1:2018
Test Report No.	4790287034.1 issued on 2023-10-10
Additional Information	The report was revised to include technical modifications. See Page 2 for additional information

Certification Manager
Thomas Wilson

Certification Body

This is to certify that representative sample(s) of the Product described herein ("Certified Product") have been investigated and found in compliance with the Standard(s) indicated on this License, in accordance with the ENEC Requirements. The Designated License holder is entitled to use the ENEC 15 Mark (as shown in annex 1) for the Certified Product manufactured at the production site(s) identified above in accordance with the ENEC Mark Service Agreement including without limitation the ENEC Mark Testing and Certification Services Service Terms. Only those Products bearing the ENEC Mark should be considered as being covered by UL's ENEC Mark Service. This License shall remain valid unless terminated earlier in accordance with the Service Agreement including without limitation if the Standard identified on this License is amended or withdrawn prior the Date of Withdrawal of conflicting Standard(s).

UL International Demko A/S, Borupvang 5A, DK-2750
Ballerup, Denmark, Tel. +45 44 85 65 65, info.dk@ul.com
www.ul.com



ENEC LICENSE

License No. ENEC-04005-M2
Page 2/3
Date of Issue 2023-10-12

Ratings:

Variants:

Main Model:

CEL550M (with Motion-Sensor), 24-240 V DC/AC 50/60 Hz, Class II, IP 20, ta = 55 °C , max. 5.1 W

Variant:

CEL550 (without Motion-Sensor), 24-240 V DC/AC 50/60 Hz, Class II, IP 20, ta = 55 °C , max. 5.1 W

Additional information:

The original report was modified to include the following changes/additions:

- Update Critical component information
- Correct of rated power
- Correct Summary of Compliance section
- Correct ratings typo
- Add note to National Differences enclosure

This Certificate replaces earlier issued ENEC Certificate No. ENEC-04005-M1 dated 2023-05-08.

Certification Body


This is to certify that representative sample(s) of the Product described herein ("Certified Product") have been investigated and found in compliance with the Standard(s) indicated on this License, in accordance with the ENEC Requirements. The Designated License holder is entitled to use the ENEC 15 Mark (as shown in annex 1) for the Certified Product manufactured at the production site(s) identified above in accordance with the ENEC Mark Service Agreement including without limitation the ENEC Mark Testing and Certification Services Service Terms. Only those Products bearing the ENEC Mark should be considered as being covered by UL's ENEC Mark Service. This License shall remain valid unless terminated earlier in accordance with the Service Agreement including without limitation if the Standard identified on this License is amended or withdrawn prior the Date of Withdrawal of conflicting Standard(s).



Annex 1 to License No.

ENEC-04005-M2

Annex of the form of the Mark



15 is the identification number of the Certification Body

Size of the mark:

The size of the mark may be reduced on the condition that it remains legible and that the ratio $b/a=1,7$ is kept.

Certification Body

This is to certify that representative sample(s) of the Product described herein ("Certified Product") have been investigated and found in compliance with the Standard(s) indicated on this License, in accordance with the ENEC Requirements. The Designated License holder is entitled to use the ENEC 15 Mark (as shown in annex 1) for the Certified Product manufactured at the production site(s) identified above in accordance with the ENEC Mark Service Agreement including without limitation the ENEC Mark Testing and Certification Services Service Terms. Only those Products bearing the ENEC Mark should be considered as being covered by UL's ENEC Mark Service. This License shall remain valid unless terminated earlier in accordance with the Service Agreement including without limitation if the Standard identified on this License is amended or withdrawn prior the Date of Withdrawal of conflicting Standard(s).