


Floor standing enclosures

















Mild steel combinable version VME

MOUNTING INSTRUCTIONS

7697-0502-32 REV.5











WARNING: When mounting on or over a combustible surface, a floor plate of at least 1.43 mm galvanized or 1.6 mm uncoated steel extended at least 150 mm beyond the equipment on all sides must be installed.

WARNING: In order to maintain the environmental integrity of the enclosure, devices with the same environmental ratings shall be used to close openings in customized enclosure.

MCS








MCD









COMBINABLE ENCLOSURE

H	A
1100	175
1400	325
1600	425
1800	525
2000	625
2200	725









SEMI-COMPACT ENCLOSURE









Ref.	Pic.	Qty.
A		2
B		4




Metal Guider



Standard Locking System













Lift Handle Locking System










SW3

MOUNTING THE LIFT HANDLE









Standard Locking System








Lift Handle Locking System







Ref.	Pic.	Qty.
A		8
B		2
C		2
D		16
E		2
F		2









H	A
1100	175
1400	325
1600	425
1800	525
2000	625
2200	725








MOUNTING LSEL

Ref.	Pic.	Qty.
A		6
B		4
C		8
D		1
E		1





Ref.	Pic.	D (mm)	<800	≥800
A	M6x12		2	4
B	M12x20		4	4
C	M12		4	4



* - Used on enclosures 800mm deep and above.








T25




T30

MCS BACK PANEL

Ref.	Pic.	W (mm)	<1000	≥1000
A			-	2
B			16	18



H	A	B
1100	-	350
1400	325	375
1600	425	475
1800	525	575
2000	625	675
2200	725	775




* - Used on enclosures 1000mm wide and above.



BOTTOM PLATE

Ref.	Pic.	Qty.
A	St. 5.5x10	6/8/12/16
B	M5x10	4
C	Washer	5/7/10/14




* - Used only on 1200mm wide enclosures.

VME MTS + MPW


Ref.	Pic.	Qty.
A	MTS	1
B	MPW	1

Double door



MPW

MTS




Single door


A. MTS - Transversal sliding profiles



Ref.	Pic.	Qty.
A		4
B		4




1. Top mounting



Torque
8-10 Nm

2. Bottom mounting



MTS





B

A

B. MPW - Wide mounting plate




Ref.	Pic.	Qty.
A		4
B		4



SPM


Ref.	Pic.	Qty.
A		6/8/9
B	 M4x14	6/8/9
C		2

Side panel mounting



* - Used only on enclosures 800 mm deep and above.

Retainer mounting







NOTE: Retainers are delivered pre-assembled.

SPM







Ref.	Pic.	Qty.
A		1
B	 M6x16	1
C		1

For the old design frame (800 mm in depth or more), the following additional steps are required:









Ref.	Pic.	Qty.
A		8
B		6
C		12
D		6





Ref.	Pic.	Qty.
A		4
B		4
C		2
D		4

















CCM 04

Ref.	Pic.	Qty.
A		4
B		8

MOUNTING










Note: It is mandatory for all four brackets to be installed at all four corners !

The fixation holes can be used to better fix the bracket to the frame, using cage nuts and screws !








DHN 180



Ref.	Pic.	Qty.
A	 M6x12	8





DHN 180 DOOR ADJUSTMENT





CNM

Ref.	Pic.	Qty.
A		1

