

PermaGround Cast Beam Bonding Clamp





nVent ERICO PermaGround Cast Beam Bonding Clamp is a device used to establish a secure electrical connection between a cable and a flat metal object, like an I-beam or channel iron. It's designed for applications where grounding or bonding of electrical systems is necessary, ensuring the safe flow of electrical current.

FEATURE

- Clamp for bonding cable to flat metal objects such as I-beams, angle irons and channel irons



Part Number	Conductor Size, UL	Main/Run Conductor Range	Material	Finish	Flange Thickness FT	Depth D	Width W	Unit Weight	Complies With	Certifications
GH-1	–	4 - 8 AWG	Copper	Bare	0.25	1.251"	1.25	0.409	UL 467	–
GM-1	–	4 - 8 AWG	Copper	Bare	0.25	1.087"	0.9	0.103	UL 467	–
GM-2	–	4 - 2/0 AWG	Copper	Bare	0.25	1.351"	0.97	0.2	UL 467	–
GM-3	–	2/0 - 250 kcmil	Copper	Bare	0.25	1.902"	1.28	0.371	UL 467	–
GM-4	–	500 - 300 kcmil	Copper	Bare	0.25	2.262"	1.4	0.569	UL 467	–
GM-5	–	500 - 700 kcmil	Copper	Bare	0.25	1¾"	3	0.25	UL 467	–
LPA559	Class 1 - Class 2 (4/0 Max)	–	Aluminum	Bare	¼" Max	2¼"	1.6"	0.14 lb	–	E202878-Combined_CoC, E202878-Combined_CoC
LPC559	Class 1 - Class 2 (4/0 Max)	–	Copper	Bare	¼" Max	2¼"	1.6"	0.39 lb	–	E202878-Combined_CoC, E202878-Combined_CoC
LPC559L	Class 1 - Class 2 (4/0 Max)	–	Copper	Tinned	¼" Max	2¼"	1.6"	0.39 lb	–	E202878-Combined_CoC, E202878-Combined_CoC



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE