


DESIGN_(PDU)
ENGINEERING

COMBO RECEPTACLE




COMBO C13/C15
10A, 250V MAX
RATED OUTPUT


COMBO C13/C15/C19
16A, 250V MAX
RATED OUTPUT

STANDARD
RECEPTACLES

RECEPTACLE



COMBO C13/C15
10A, 250V MAX RATED OUTPUT



COMBO C13/C15/C19
16A, 250V MAX RATED OUTPUT


INPUT PLUG

(DEFAULT)





IEC 60309, 4P, 5W, 6H
IP44(SPLASHPROOF)
60A/63A, 415V MAX RATED INPUT
(48A DERATED)

(OPTIONAL)



IEC 60309, 4P, 5W, 6H
IP67(WATERTIGHT)
60A/63A, 415V MAX RATED INPUT
(48A DERATED)



NOTES:
1. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE AND LOCAL CODES.
2. SEE PRODUCT DOCUMENTATION FOR FURTHER INFORMATION



THIS DRAWING AND SPECIFICATIONS HEREIN ARE THE PROPERTY OF CIS GLOBAL AND SHALL NOT BE COPIED, REPRODUCED OR USED IN WHOLE OR IN PART, AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION FROM CIS GLOBAL. THIS DRAWING IS BASED UPON LATEST AVAILABLE INFORMATION AND IS SUBJECT TO CHANGE WITHOUT NOTICE

TITLE:
*Advantage Series
Metered & Switched
PER OUTLET*

PROJECT:
enLOGIC

UNLESS NOTED, DIMENSIONS ARE IN MILLIMETERS & TOLERANCES ARE:
X . ±1 MM X' ±1"
X.X ±0.5 MM X.X' ±0.5"
X.XX ±0.25 MM
Ø X.X ±0.3 MM
Ø X.XX ±0.10 MM
BRACKETED DIMENSIONS ARE IN INCHES FOR REFERENCE ONLY

THIRD ANGLE PROJECTION
INTERPRET PER ASME Y14.5M-1994

SKU NO:
RP6910WXYZ_DA
DRAWN BY: Luojingbo
ENGINEER: Hanson
APPROVED BY: Hanson

REV.
E2
2022-09-27
2022-11-21
2022-11-21

SCALE: 1:1 (DO NOT SCALE DRAWING)
SHEET 2 OF 3
SIZE: A1

enLOGIC

RACK Power Distribution Unit

Metered & Switched per outlet

SKU #: EN6910-WXYZ

Model#: EP162048-0062-C(NA)/EP162063-0062-C(EU)

INPUT: 200-240/346-415VAC, 3PHASE, WYE, 50/60Hz, 48A(NA), OR 200-240/346-415VAC, 3PHASE, WYE, 50/60Hz, 63A(EU)

OUTPUT: C13/C15 COMBO; 200-240VAC, 10A per outlet

C13/C15/C19 COMBO; 200-240VAC, 16A max per outlet

48A Total(NA) OR 63A Total(EU)

MAC0 Address:XX-XX-XX-XX-XX-XX

MAC1 Address:XX-XX-XX-XX-XX-XX

Made In XXXXX

CIS Global LLC

1601 W COMMERCE

CT TUCSON,

AZ 85746

EN 6 9 1 0 - W X Y Z

Serial Number

XXXXXXXXXX

THIS DEVICE COMPLIES WITH PART 15 OF THE FCC RULES.

OPERATION IS SUBJECT TO THE FOLLOWING TWO CONDITIONS:

(1) THIS DEVICE MAY NOT CAUSE HARMFUL INTERFERENCE,

AND (2) THIS DEVICE MUST ACCEPT ANY INTERFERENCE RECEIVED,

INCLUDING INTERFERENCE THAT MAY CAUSE UNDESIRABLE OPERATION.

CAN ICES-3(A)/NMB-3(A)

DESIGN^(PDU)
ENGINEERING

NOTES:
1. INTERNAL WIRING:
WIRE TYPE:
LINE 1/R/X COLOR:
LINE 1/R/X COLOR:
LINE 1/R/X COLOR:
NEUTRAL COLOR:
EARTH GROUND COLOR:
UL AWM 1015, 10 & 12 & 18AWG
BLACK
ORANGE
RED
WHITE
GREEN/YELLOW STRIPE

COMPLIANCE LABEL

INTERNAL WIRING SCHEMATIC

NOTES:

- INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE AND LOCAL CODES.
- SEE PRODUCT DOCUMENTATION FOR FURTHER INFORMATION
- THIS DRAWING DEPICTS THE POWER SYSTEM CONNECTIONS AND IS NOT REPRESENTATIVE OF THE PHYSICAL LAYOUT. PLEASE REFER TO MECHANICAL DRAWINGS FOR PHYSICAL LAYOUT.

| | | | | |
|--|---|---|---|---|
| <div><div>enLOGICby nvent</div><div>THIS DRAWING AND SPECIFICATIONS HEREIN ARE THE PROPERTY OF CIS GLOBAL AND SHALL NOT BE COPIED, REPRODUCED OR USED IN WHOLE OR IN PART, AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION FROM CIS GLOBAL. THIS DRAWING IS BASED UPON LATEST AVAILABLE INFORMATION AND IS SUBJECT TO CHANGE WITHOUT NOTICE</div></div> | <div>TITLE:<div>Advantage Series</div>Metered & Switched PER OUTLET</div> <div>PROJECT:<div>enLOGIC</div></div> | <div>UNLESS NOTED, DIMENSIONS ARE IN MILLIMETERS & TOLERANCES ARE: X. ±1 MM X.X ±0.5 MM X.XX ±0.25 MM ØX.X ±0.3 MM ØX.XX ±0.10 MM BRACKETED DIMENSIONS ARE IN INCHES FOR REFERENCE ONLY ⊕ THRID ANGLE PROJECTION INTERPRET PER ASME Y14.5M-1994</div> | <div>SKU NO: EN6910-WXYZ_DA</div> <div>DRAWN BY: Lurongfeng</div> <div>ENGINEER: Hanson</div> <div>APPROVED BY: Hanson</div> <div>SCALE: 1:1 (DO NOT SCALE DRAWING)</div> | <div>REV. E1</div> <div>2023-01-28</div> <div>2023-01-28</div> <div>2023-01-28</div> <div>SHEET 3 OF 3</div> <div>SIZE A1</div> |
|--|---|---|---|---|