

# nVent ERICO PermaGround Compression Connector, Cross Grid



The nVent ERICO PermaGround Compression Connector, Cross Grid, is engineered to provide exceptional grounding performance and reliability. Constructed of high-strength copper alloy, this connector ensures maximum conductivity and durability. It is labeled with wire size and die index, facilitating easy identification and tooling recommendations. The connector can be adjusted prior to installation, making it ideal for accommodating misaligned cross grids. Prefilled with DE-OX oxide-inhibiting compound, it prevents oxides from forming and ensures long-term reliability.


## FEATURES

- Range-taking design
- Suitable for direct burial in earth or concrete
- Suitable for installation in all weather conditions

**Material:** Copper  
**Conductor Type:** Solid, Stranded  
**Direct Burial:** Yes



Part Number	Die Index	Length L	Height H	Width W	Main/Run Conductor Range	Tap Conductor Range	Unit Weight
GGA-1	0	2.5"	1.09"	2.5"	2 – 6 AWG	2 – 6 AWG	0.43 lb
GGA-2	997	2.5"	1.09"	2.5"	250 kcmil – 1/0 AWG	2 – 6 AWG	0.45 lb
GGA-3	997	2.5"	1.66"	2.5"	250 kcmil – 2 AWG	250 kcmil – 2 AWG	0.83 lb
GGA-4	998	2.5"	1.09"	2.5"	500 – 250 kcmil	2 – 6 AWG	0.68 lb
GGA-5	997	2.5"	1.66"	2.5"	500 – 250 kcmil	250 kcmil – 2 AWG	1.07 lb
GGA-6	1011	2.5"	2.28"	2.5"	500 – 250 kcmil	500 – 250 kcmil	1.8 lb



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**