

nVent ERICO PermaGround Compression Connector, Ground Plate





The nVent ERICO PermaGround Compression Connector, Ground Plate, is designed to provide a reliable and efficient grounding solution. This product is for applications that demand high strength and conductivity, ensuring a secure and durable connection. Its cast copper alloy body and pre-filled De-Ox Oxide Inhibitor enhance durability and performance. This design provides versatility and convenience for various grounding applications.

FEATURES

- Cast copper alloy body with underside tapped hole
- Available in two and four-hole NEMA spacing
- Suitable for installation in all weather conditions

Complies With: UL® 467
Conductor Type: Solid, Stranded
Connection Type: Crimp
Direct Burial: Yes
Material: Copper
Number of Crimps: 1

Part Number	Main/Run Conductor Range	Die Index	Length L	Width W	Height H	Unit Weight
CGP2-2250	250 kcmil – 2	15G86R	5.78"	2"	3.625"	1.94 lb
CGP2-250500	500 – 250 kcmil	15G126R	5.4"	2"	3.625"	2.5 lb
CGP4-2250	250 kcmil – 2	15G86R	5.78"	3.125"	4.0313"	2.5 lb
CGP4-250500	500 – 250 kcmil	15G126R	5.9"	3.125"	4.0313"	3.36 lb



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE