



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF CIS. ANY REPRODUCTION IN PART OR WHOLE WITHOUT WRITTEN PERMISSION OF CIS IS PROHIBITED.


REVISIONS					
ECN/ECO	PLACES	REV.	DESCRIPTION	SIGN	DATE
		E1	Design Release	Aric Wang	2020.09.10
CIS-ECN-2101-0046		E2	SHEET FORMAT UPDATE, ADD GROUND SYMBOL	Luo jingbo	2021-02-19




LEFT VIEW




REAR VIEW



RIGHT VIEW



FRONT VIEW




BOTTOM VIEW


PLUG/RECEPTACLE BLOCK



PLUG
IEC 60309, 2P 3W, 6H
IP44 (SPASHPROOF)
32A, 200 - 250V MAX RATED INPUT



RECEPTACLES
IEC 60320/C19
16A, 250V MAX RATED OUTPUT




RECEPTACLES
IEC 60320/C13
10A, 250V MAX RATED OUTPUT

SPECIFICATION:

UNIT TYPE:
ORIENTATION:
OUTLET QTY & TYPE:
INPUT VOLTAGE:
INPUT CURRENT:
BREAKER QTY & TYPE:
INPUT PHASE:
RATED POWER:
INPUT PLUG:
INPUT POWER CORD:
REGULATORY STANDARD:

MONITORED SWITCHED
VERTICAL, 0U FULL, WIDE
(38)C13, (6) C19
200-240VAC
32A
(2) 16AMP, SIGLE-POLE
SINGLE-PHASE
7.4 kVA
SEE IDENTIFICATION TABLE
SEE IDENTIFICATION TABLE
RoHS COMPLIANT

IDENTIFICATION TABLE
EN2337-WXYZ



MODEL IS SHOWN IN STANDARD DEFAULT CONFIGURATION
SEE IDENTIFICATION TABLE FOR OPTIONAL CONFIGURATIONS
ORDERABLE BASED ON SKU NUMBER WITH DASH SUFFIX

NOTES:

- PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSIONS ARE IN [INCHES]
- SEE PRODUCT OVERVIEW AND SPECIFICATIONS SHEET FOR FURTHER INFORMATION
STANDARD INPUT POWER CORD LENGTH IS 3000MM[118.0IN]
- DETAILED INSTALLATION INSTRUCTIONS CAN BE FOUND INTHE QUICK START GUIDE
- BRACKET KITS TO MOUNT TO SPECIFIC RACKS & ENCLOSURES ARE AVAILABLE AS OPTIONS
- CONNECT SUPPLEMENTARY EXTERNAL EXTERNAL EARTH GROUND TO THE 10-32 SIZE THREADED NUT

UNLESS NOTED, DIMENSIONS IN MILLIMETERS & TOLERANCES ARE: X. ± 1 MM X.X ± 0.5 MM X.XX ± 0.20 MM ØX.X ± 0.4 MM ØX.XX ± 0.20 MM		DESIGNER & DATE: Aric Wang 2020-09-10 STANDARDIZATION/CHECKER & DATE: Aric Wang 2021-02-19 DFM & DATE: Talon Lv 2021-02-19 APPROVER & DATE: Hanson Xu 2021-02-19 ITEM WEIGHT (REFERENCE ONLY):		THIRD ANGLE PROJECTION	
IF 2D AND 3D DIFFER, 2D SHALL TAKE PRECEDENCE		MATERIAL: Assembly		SCALE: N/A	

CISGLOBAL

EN2.0 PDU

EN2337-WXYZ_DA

E2

SHEET 1 OF 2

enLOGIC

SKU #: EN2337-WXYZ
Model #: EP21032-0033
INPUT: 200-240VAC, 1Ø, 50/60Hz, 32A
OUTPUT: C13; 200-240VAC, 10A per outlet
C19; 200-240VAC, 16A per outlet
32A Total
MAC0 Address:XX-XX-XX-XX-XX
MAC1 Address:XX-XX-XX-XX-XX

Power Distribution Unit



CIS Global LLC
1791 W Dairy Place,
Suite 185, Tucson,
Arizona 85705



SKU#:



Serial Number




XXXXXXX

Made In XXXXX

Mfr.Name:XXXXXXXXXX

- NOTES:
- 1.INTERNAL WIRING:
WIRE TYPE: UL AWM 1015, 12&18AWG
LINE 1/R/X COLOR: BROWN
EARTH GROUND COLOR: GREEN/YELLOW STRIPE
NEUTRAL WIRE COLOR: BLUE
- 2.FOR FINISHED GOOD PART NUMBER SEE IDENTIFICATION

COMPLIANCE LABEL



INTERNAL WIRING SCHEMATIC

UNLESS NOTED, DIMENSIONS IN MILLIMETERS & TOLERANCES ARE: X. ± 1 MM X.X ± 0.5 MM X.XX ± 0.20 MM ØX.X ± 0.4 MM ØX.XX ± 0.20 MM BRACKETED DIMENSIONS ARE IN INCHES FOR REFERENCE ONLY  THIRD ANGLE PROJECTION IF 2D AND 3D DIFFER, 2D SHALL TAKE PRECEDENCE	DESIGNER & DATE: Aric Wang 2020-09-10	CISGLOBAL		
	STANDARDIZATION/CHECKER & DATE: Aric Wang 2021-02-19			
	DFM & DATE: Talon Lv 2021-02-19	DESCRIPTION: EN2.0 PDU		
	APPROVER & DATE: Hanson Xu 2021-02-19			
	ITEM WEIGHT (REFERENCE ONLY):	P/N: EN2337-WXYZ_DA		REV: E2
MATERIAL: Assembly	SCALE: N/A		SIZE: N/A	SHEET 2 OF 2