






THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF CIS. ANY REPRODUCTION IN PART OR WHOLE WITHOUT WRITTEN PERMISSION OF CIS IS PROHIBITED.

REVISIONS					
ECN/ECO	PLACES	REV.	DESCRIPTION	SIGN	DATE
		E1	Design Release	Wanbin Liu	2020.05.12
CIS-ECN-2101-0046		E2	SHEET FORMAT UPDATE, ADD GROUND SYMBOL	Luo jingbo	2021-02-17



PLUG/RECEPTACLE BLOCK

PLUG
IEC 60309, 4P 5W, 6H
IP44 (SPASHPROOF)
32A, 346 - 415V MAX RATED INPUT

RECEPTACLES
IEC 60320/C19
16A, 250V MAX RATED OUTPUT


RECEPTACLES
IEC 60320/C13
10A, 250V MAX RATED OUTPUT

SPECIFICATION:

UNIT TYPE:
ORIENTATION:
OUTLET QTY & TYPE:
INPUT VOLTAGE:
INPUT CURRENT:
BREAKER QTY & TYPE:
INPUT PHASE:
RATED POWER:
INPUT PLUG:
INPUT POWER CORD:
REGULATORY STANDARD:

MONITORED INPUT
VERTICAL, 0U FULL, 2-SIDE
(36)C13, (12) C19
200-240/346-415VAC
32A
(6) 16AMP, SIGLE-POLE
THREE-PHASE, WYE
22.0 kVA
SEE IDENTIFICATION TABLE
SEE IDENTIFICATION TABLE
RoHS COMPLIANT

**IDENTIFICATION TABLE
EN2812-WXYZ**



MODEL IS SHOWN IN STANDARD DEFAULT CONFIGURATION
SEE IDENTIFICATION TABLE FOR OPTIONAL CONFIGURATIONS
ORDERABLE BASED ON SKU NUMBER WITH DASH SUFFIX

- NOTES:
- PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSIONS ARE IN [INCHES]
 - SEE PRODUCT OVERVIEW AND SPECIFICATIONS SHEET FOR FURTHER INFORMATION
STANDARD INPUT POWER CORD LENGTH IS 3000MM[118.0IN]
 - DETAILED INSTALLATION INSTRUCTIONS CAN BE FOUND INTHE QUICK START GUIDE
 - BRACKET KITS TO MOUNT TO SPECIFIC RACKS & ENCLOSURES ARE AVAILABLE AS OPTIONS
 - CONNECT SUPPLEMENTARY EXTERNAL EXTERNAL EARTH GROUND TO THE 10-32 SIZE THREADED NUT

UNLESS NOTED, DIMENSIONS IN MILLIMETERS & TOLERANCES ARE:			DESIGNER & DATE: Wanbin Liu2020-05-12		CISGLOBAL			
X. ± 1 MM X.X ± 0.5 MM X.XX ± 0.20 MM ØX.X ± 0.4 MM ØX.XX ± 0.20 MM			STANDARDIZATION/CHECKER & DATE: Aric Wang2021-02-17					
BRACKETED DIMENSIONS ARE IN INCHES FOR REFERENCE ONLY			DFM & DATE: Talon Lv2021-02-17		DESCRIPTION: EN2.0 PDU			
			APPROVER & DATE: Hanson Xu2021-02-17					
			ITEM WEIGHT (REFERENCE ONLY):		PIN: EN2812-WXYZ_DA		REV: E2	
THIRD ANGLE PROJECTION 			MATERIAL: Assembly		SCALE: N/A		SIZE: N/A	SHEET 1 OF 2
IF 2D AND 3D DIFFER, 2D SHALL TAKE PRECEDENCE								

enLOGIC

SKU #: EN2812-WXYZ

Model #: PP22032-0017

INPUT: 200-240/346-415VAC,WYE,3Phase,50/60Hz,32A

OUTPUT: C13; 200-240VAC, 10A per outlet

C19; 200-240VAC, 16A per outlet

32A Total

MAC0 Address:XX-XX-XX-XX-XX-XX

MAC1 Address:XX-XX-XX-XX-XX-XX

Power Distribution Unit



CIS Global LLC
1731 W Dairy Place,
Suite 185, Tucson,
Arizona 85705



SKU#:



EN2812-WXYZ

Serial Number



XXXXXXXXXX

Made In XXXXX

Mfr.Name: xxxxxxxxxxxxxxxxxxxxxxxx

NOTES:

1.INTERNAL WIRING:

WIRE TYPE:

LINE 1/R/X COLOR:

LINE 2/S/Y COLOR:

LINE 3/T/Z COLOR:

EARTH GROUND COLOR:

NEUTRAL WIRE COLOR:

UL AWM 1015, 10&12&18AWG

BROWN

BLACK


WHITE

GREEN/YELLOW STRIPE

BLUE

2.FOR FINISHED GOOD PART NUMBER SEE IDENTIFICATION

COMPLIANCE LABEL



INTERNAL WIRING SCHEMATIC

UNLESS NOTED, DIMENSIONS IN MILLIMETERS & TOLERANCES ARE: X. ± 1 MM X.X ± 0.5 MM X.XX ± 0.20 MM ØX.X ± 0.4 MM ØX.XX ± 0.20 MM THIRD ANGLE PROJECTION IF 2D AND 3D DIFFER, 2D SHALL TAKE PRECEDENCE	DESIGNER & DATE: Wanbin Liu 2020-05-12	CISGLOBAL		
	STANDARDIZATION/CHECKER & DATE: Aric Wang 2021-02-17			
	DFM & DATE: Talon Lv 2021-02-17	DESCRIPTION: EN2.0 PDU		
	APPROVER & DATE: Hanson Xu 2021-02-17			
ITEM WEIGHT (REFERENCE ONLY):		P/N:	EN2812-WXYZ_DA	
MATERIAL: Assembly		REV:	E2	
SCALE: N/A			SIZE: N/A	SHEET 2 OF 2