


RACK-MOUNTABLE ASSEMBLIES



INDUSTRY STANDARDS

UL recognized

- CSA Certified Motors
- CE

APPLICATION


Fan trays are a versatile solution to cooling card cages and racks. Redundant cooling with optional failure detection makes this air mover the obvious choice for sensitive equipment. Minimal rack space and repositionable fans are suited to today's smaller enclosures.

FEATURES


- Slim 1.75 in. (44 mm) Panel Height
- 19-in. rack mountable
- Field adjustable fan strips to optimize air flow
- Easy access to fan tray from front and back
- Simplified installation without the need for side access
- Support bracket
- Exhaust Guard
- 6-inch Power Cord AC trays, Terminal block on DC trays
- Permanently lubricated ball bearing motors
- 100% functionally tested

SPECIFICATIONS


- 115/230 VAC
- 50/60 Hz




Performance Curves (Inches of Water to CFM)



Performance Curves (Pa to m3/hr)





Performance Data **Rack-Mountable Assemblies**

ELECTRICAL DATA		
Rated Voltage	115 VAC	230 VAC
Frequency (Hz)	50/60	50/60
RPM	3100	3100
Nominal Current Maximum (Amps)	0.4	0.2
Power Consumption Maximum (Watts)	42	42
Maximum Operating Temperature (°F/°C)	158/70	
UEB17H		
Catalog Numbers	UEB17H115	UEB17H230
Nominal Current Maximum @50/60 Hz (Amps)	.4	.2
Power Consumption Maximum @ 50/60 Hz (Watts)	42	42
Free Airflow @ 50/60 Hz (CFM)*	315	315
Free Airflow @ 50/60 Hz (m ³ /hr.)*	536	536
Number of Fans	3	
Unit Dimensions H x W x D (In./mm)	1.75 x 19.00 x 8.00/44 x 482 x 203	
Weight (lb./kg)	7.8/3.4	7.8/3.4
2EB17H		
Catalog Numbers	2EB17H115	2EB17H230
Nominal Current Maximum @50/60 Hz (Amps)	.9	.5
Power Consumption Maximum @ 50/60 Hz (Watts)	84	84
Free Airflow @ 50/60 Hz (CFM)*	630	630
Free Airflow @ 50/60 Hz (m ³ /hr.)*	1071	1071
Number of Fans	6	
Unit Dimensions H x W x D (In./mm)	1.75 x 19.00 x 18.75/44 x 482 x 476	
Weight (lb./kg)	10.2/4.5	10.2/4.5
3EB17H		
Catalog Numbers	3EB17H115	3EB17H230
Nominal Current Maximum @50/60 Hz (Amps)	1.4	.8
Power Consumption Maximum @ 50/60 Hz (Watts)	126	126
Free Airflow @ 50/60 Hz (CFM)*	945	945
Free Airflow @ 50/60 Hz (m ³ /hr.)*	1607	1607
Number of Fans	9	
Unit Dimensions H x W x D (In./mm)	1.75 x 19.00 x 18.75/44 x 482 x 476	
Weight (lb./kg)	12.5/5.5	12.5/5.5